






型号	CKT	A	B	C
XY-PHB2.0-4A51-G	2*2	2.00	6.00	3.00
XY-PHB2.0-6A51-G	2*3	4.00	8.00	3.00
XY-PHB2.0-8A51-G	2*4	6.00	10.00	3.00
XY-PHB2.0-10A51-G	2*5	8.00	12.00	5.00
XY-PHB2.0-12A51-G	2*6	10.00	14.00	7.00
XY-PHB2.0-14A51-G	2*7	12.00	16.00	9.00
XY-PHB2.0-16A51-G	2*8	14.00	18.00	11.00
XY-PHB2.0-18A51-G	2*9	16.00	20.00	13.00
XY-PHB2.0-20A51-G	2*10	18.00	22.00	15.00
XY-PHB2.0-22A51-G	2*11	20.00	24.00	17.00
XY-PHB2.0-24A51-G	2*12	22.00	26.00	19.00
XY-PHB2.0-26A51-G	2*13	24.00	28.00	21.00
XY-PHB2.0-28A51-G	2*14	26.00	3.00	23.00
XY-PHB2.0-30A51-G	2*15	28.00	32.00	25.00
XY-PHB2.0-32A51-G	2*16	30.00	34.00	27.00
XY-PHB2.0-36A51-G	2*18	34.00	38.00	31.00
XY-PHB2.0-40A51-G	2*20	38.00	42.00	35.00
XY-PHB2.0-44A51-G	2*22	42.00	46.00	39.00

技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ 。
3. 适用线规: AWG#28~#22。
4. 额定电压: 250V DC/AC(rms)。
5. 额定电流: 3.0A AC, DC。
6. 接触电阻: $\leq 20\text{m}\Omega$ 。
7. 耐压值: 800V AC/minute。
8. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。

PCB WELDING DRAWING (TOLERANCE: ± 0.05)

序号	名称	材质
3	2.0A型双排立式WTB底座	LCP UL94V-0 本色
2	2.0A型立式(连续)端子	铜合金/表面镀锡
1	2.0A型双排立式WTB嵌芯	LCP UL94V-0 本色

DIMENSION IN mm		TOLERANCE UNLESS OTHERWISE SPECIFIED		APR. Alex		TITLE: 2.0 Pitch A型双排立式WTB	
.X ± 0.3	X.* $\pm 5^{\circ}$	.XX ± 0.25	.X.* $\pm 1^{\circ}$	CHK. Jack		DWG NO. XXY-PHB2.0-NA51-G	
.XXX ± 0.15				DRA. Can		PROJ.	CUSTOMER DRAWING
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A				