









RECOMMEND PCB LAYOUT
TOLERANCE: ± 0.05
TOP VIEW

MATERIALS

1. HOUSING : LCP , BLACK.
2. TERMINAL : BRASS,
PLATING : GOLD PLATED ON CONTACT AREA,
TIN PLATED ON SOLDER TAILS.
3. SHELL : BRASS,
PLATING : NICKEL PLATED OVERALL.
4. EMI SHIELD : STAINLESS STEEL.



SPECIFICATION

1. CURRENT RATING : 0.5 A. MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE :
500V AC R.M.S. FOR 1 MINUTE.
3. INSULATION RESISTANCE : 100M Ω MIN.AT 500V DC.
4. CONTACT RESISTANCE : 30m Ω MAX.
5. OPERATING TEMPERATURE : -25°C TO +85°C.
6. INSERTION FORCE : 4.5Kgf MAX.
7. WITHDRAWING FORCE : 1Kgf ~ 4Kgf.




深圳市华宇创精密电子有限公司


TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI2.1 A TYPE SMT带耳 8.78螺丝孔	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW176-HDMI A19-878B	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2606161152	SHEET NO. 1 OF 1



PACKAGE :

1. CORTON SIZE: 400x400x380mm (LxWxH)
2. 250 PCS/REEL
3. 7 REEL/CARTON = 1750PCS



 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO:
			SHEET NO. 1 OF 1