












RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS=1.20±0.05mm (TOP VIEW)DEFAULT TOL ±0.05



NOTES:

1. ELECTRICAL CHARACTERISTICS:

1-1. CURRENT RATING: 0.5A Max

1-2. VOLTAGE RATING: 40V AC Max

1-3. INITIAL CONTACT RESISTANCE EXCLUDING CONDUCTOR RESISTANCE:
30mΩ MAX. AFTER TEST: CHANGE OF 10mΩ MAX.

1-4. INSULATION RESISTANCE: 100MΩ MIN. @ 500V DC.

1-5. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE.

2. MECHANICAL CHARACTERISTICS:

2-1. INSERTION FORCE: 4.5Kgf MAX.

2-2. WITHDRAWAL FORCE: 1.0~4.0Kgf.

3. LIFE TEST: 10,000 CYCLES.

4. TEMPERATURE

4-1. OPERATING TEMPERATURE: -40℃~+85℃

4-2. STORAGE TEMPERATURE: -60℃~+105℃




5. SOLDERABILITY: REFLOW SOLDERING OVEN TEMPERATURE 260° 5sec

C	CONTACT	19	C2680-H	GOLD 1u" Min ON CONTACT AREA, MATTE TIN 80u" ON SOLDER AREA. 50u" MIN NI UNDER PLATING OVERALL
B	SHELL	1	SUS201	50u" MIN. NICKEL
A	HOUSING	1	LCP+30%G.F UL 94V-0	BLACK
NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR




深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI2.1 A TYPE 立式贴片15.0H	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW177-HDMI A19-150B	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2606161512	SHEET NO. 1 OF 1



NOTE:

1. PEELING SPEED: 300mm/MINUTE
2. PEELING RESISTANCE: 10g~130g
3. PEELING ANGLE: 165°~180°



150	8	1200
PCS/ REEL	REELS/ CARTON	QUANTITY



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图
UNIT: mm [inch] SCALE:1:1 SIZE: A4	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. MOLD NO.
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: SHEET NO. 1 OF 1