








PCB LAYOUT



技术要求Notes:

1.外观质量Appearance quality:

a.金属表面镀层不能有明显损伤;

Coating on metal surface can not be damaged obviously;

b.塑壳表面不能有明显的变形或开裂;

No obvious deformation or cracking can be observed on the surface of

the Housing;

c.产品表面应保持清洁;

Product surface should be kept clean;

2.工作温度 Working temperature: $-25^{\circ}\text{C}\sim+105^{\circ}\text{C}$;

3.额定电压 Voltage Rating: Max 50V (AC/Effective value rms)/DC;

4.额定电流 Current Rating: Max 1A (AC/Effective value rms)/DC;

5.接触电阻 Contact resistance: Max 20 m Ω ;

6.绝缘电阻 Insulation resistance: Min 100M Ω ;

7.耐压 Withstanding voltage: 500V AC(50 Hz, Effective value: 1 min);

8.环保要求应符合RoHS2.0标准

Environmental requirements should meet RoHS2.0 standards.

3	焊片Fitting Nail	磷铜 Phosphor copper	2	镀锡Tin-plated	
2	端子Terminal	磷铜 Phosphor copper	N	镀锡Tin-plated	
1	底座Housing	LCP UL94-V0	1	本色Natural color	
序号 No.	名称 Part Name	材料 Material	数量 Qty	备注 Remark	

16	15.00	18.00	16.60
15	14.00	17.00	15.60
14	13.00	16.00	14.60
13	12.00	15.00	13.60
12	11.00	14.00	12.60
11	10.00	13.00	11.60
10	9.00	12.00	10.60
9	8.00	11.00	9.60
8	7.00	10.00	8.60
7	6.00	9.00	7.60
6	5.00	8.00	6.60
5	4.00	7.00	5.60
4	3.00	6.00	4.60
3	2.00	5.00	3.60
2	1.00	4.00	2.60
孔位 CKT NO.	DIM A	DIM B	DIM C

		APPROVALS		DATE			
DRAWN		G.M.Chen		2015/5/22			
CHECKED							
APPROVALS							
PART NO.		1.0--XCPWB					
TITLE:		1.00mm Crimp Style Connectors					
ELECTRONICS CO.,LTD							
UNIT: mm		SCALE: 1:1					
DRAWING NO.							
SHEET 1 OF 1							
PROJ.							
ECN NO.		REV.		DATE.			
NEW							
DESCRIPTION.		CHANGE.		CHECK.	APPRO.		