






技术要求Notes:

1.外观质量Appearance quality:

a. 金属表面镀层不能有明显损伤;

Coating on metal surface can not be damaged obviously;

b. 塑壳表面不能有明显的变形或开裂;

No obvious deformation or cracking can be observed on the surface of the Housing;

C. 产品表面应保持清洁;

Product surface should be kept clean;

2.工作温度 Working temperature: $-25^{\circ}\text{C}\sim+105^{\circ}\text{C}$;

3. 额定电压 Voltage Rating: Max 50V [AC(Effective value rms)/DC];

4. 额定电流 Current Rating: Max 1A [AC(Effective value rms)/DC];


5. 接触电阻: Max 20 mΩ

6. **绝缘电阻** Insulation resistance: Min 100M Ω ;

7.耐压 Withstanding voltage: 500V AC(50 Hz, Effective value; 1 min);

8.环保要求应符合RoHS2.0标准

Environmental requirements should meet RoHS2.0 standards



PCB LAYOUT

3	焊片 Fitting Nail	磷铜 Phosphor copper	2	镀锡 Tin-plated
2	端子 Terminal	磷铜 Phosphor copper	N	镀锡 Tin-plated
1	基座 Housing	LCP UL94-V0	1	本色 Natural color
序号 No.	名称 Part Name	材料 Material	数量 Qty	备注 Remark

16	15.00	18.00	16.60
15	14.00	17.00	15.60
14	13.00	16.00	14.60
13	12.00	15.00	13.60
12	11.00	14.00	12.60
11	10.00	13.00	11.60
10	9.00	12.00	10.60
9	8.00	11.00	9.60
8	7.00	10.00	8.60
7	6.00	9.00	7.60
6	5.00	8.00	6.60
5	4.00	7.00	5.60
4	3.00	6.00	4.60
3	2.00	5.00	3.60
2	1.00	4.00	2.60
孔位 CKT NO.	DIM A	DIM B	DIM C

PCB LAYOUT									
		APPROVALS		DATE					
		DRAWN	G.M.Chen	2015/5/22		TITLE: 1.00mm Crimp Style Connectors			
		CHECKED				PART NO. 1.0-XXPS			
		APPROVALS							
		30° ±0.1° 10°~30° ±0.20° 5°~10° ±0.15° ~ 5° ±0.10°		ANGLE		UNIT: mm		SCALE: 1:1	SHEET 1 OF 1
	A	NEW				DRAWING NO.		PROJ. 	
ECN NO.	REV.	DATE.	DESCRIPTION.		CHANGE.	CHECK.	APPRO.		