





VER	MARK	PR. BY	DESCRIPTION	DATE

Part No	Pin	A	B
HMT-XH2. 54-WZR2P	2	2.5	7.5
HMT-XH2. 54-WZR3P	3	5.0	10.0
HMT-XH2. 54-WZR4P	4	7.5	12.5
HMT-XH2. 54-WZR5P	5	10.0	15.0
HMT-XH2. 54-WZR6P	6	12.5	17.5
HMT-XH2. 54-WZR7P	7	15.0	20.0
HMT-XH2. 54-WZR8P	8	17.5	22.5
HMT-XH2. 54-WZR9P	9	20.0	25.0
HMT-XH2. 54-WZR10P	10	22.5	27.5
HMT-XH2. 54-WZR11P	11	25.0	30.0
HMT-XH2. 54-WZR12P	12	27.5	32.5
HMT-XH2. 54-WZR13P	13	30.0	35.0
HMT-XH2. 54-WZR14P	14	32.5	37.5
HMT-XH2. 54-WZR15P	15	35.0	40.0
HMT-XH2. 54-WZR16P	16	37.5	42.5

序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Red
2	XH2.5 弯针 端子	Copper Alloy/ Tin Plating

Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 3.0A.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
X. [°] ±0.50	X. [°] ±5°	PART NO.	TITLE: XH2.5 弯针		
X.X [°] ±0.20	X.X [°] ±3°	HMT-XH2.54-WZRN			
X.XX [°] ±0.10	X.XX [°] ±1°	DESIGN: James	CUSTOMER 	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1