


Surface Mount General Purpose Silicon Rectifiers
Reverse Voltage - 50 to 1000 V
Forward Current - 5 A
FEATURES


- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Easy to pick and place
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SMC
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.22g /0.0077oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode


Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	S5A	S5B	S5D	S5G	S5J	S5K	S5M	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current	$I_{F(AV)}$	5							A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	I_{FSM}	150							A
Maximum Instantaneous Forward Voltage at 5 A	V_F	1.0							V
Maximum DC Reverse Current $T_a = 25\text{ }^{\circ}\text{C}$ at Rated DC Blocking Voltage $T_a = 125\text{ }^{\circ}\text{C}$	I_R	5 100							μA
Typical Junction Capacitance ⁽¹⁾	C_j	50							pF
Typical Thermal Resistance ⁽²⁾	$R_{\theta JA}$ $R_{\theta JC}$	35 13							$^{\circ}\text{C/W}$
Operating and Storage Temperature Range	T_j, T_{stg}	-55 ~ +150							$^{\circ}\text{C}$

⁽¹⁾ Measured at 1 MHz and applied reverse voltage of 4 V.D.C

⁽²⁾ P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.



Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance





Fig.6 Maximum Non-Repetitive Peak Forward Surge Current






PACKAGE OUTLINE

Plastic surface mounted package; 2 leads


SMC



SMC mechanical data

UNIT		A	E	D	B	A ₁	C	L	b
mm	max	2.62	7.1	6.2	8.3	0.21	0.31	1.6	3.25
	min	2.00	6.6	5.6	7.7	0.05	0.15	0.9	2.75
mil	max	103	280	244	327	8.3	12	63	128
	min	79	260	220	303	2.0	5.9	35	108

The recommended mounting pad size



Marking

Type number	Marking code
S5A	S5A
S5B	S5B
S5D	S5D
S5G	S5G
S5J	S5J
S5K	S5K
S5M	S5M