



Features

- Epitaxial planar die construction
- Built-in biasing resistors (R_1 : 10k Ω , R_2 : 47k Ω)
- Also available in lead free version
- RoHS compliant with Halogen-free

Mechanical Data

- Case: SOT-23
- Molding Compound: UL Flammability Classification Rating 94V-0
- Terminals: Matte tin-plated leads; solderability-per MIL-STD-202, Method 208




Ordering Information

Part Number	Package	Shipping Quantity
PDTC114YT	SOT-23	3000 pcs / Tape & Reel

Maximum Ratings (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
		SOT-23	
Supply Voltage	V_{CC}	50	V
Input Voltage	V_I	-6 to +40	V
Output Current	I_O	70	mA
Collector Current	$I_{C(\text{Max})}$	100	mA
Power Dissipation	P_D	200	mW
Junction Temperature Range	T_J	-55 ~ +150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 ~ +150	$^\circ\text{C}$

Marking:



Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input Voltage	$V_{I(\text{OFF})}$	$V_{CC} = 5\text{V}, I_o = 100\mu\text{A}$	0.3	-	-	V
Input Voltage	$V_{I(\text{ON})}$	$V_o = 0.3\text{V}, I_o = 1\text{mA}$	-	-	1.4	V
Output Voltage	$V_{O(\text{on})}$	$I_o = 5\text{mA}, I_i = 0.25\text{mA}$	-	-	0.3	V
Input Current	I_i	$V_i = 5\text{V}$	-	-	0.88	mA
Output Current	$I_{O(\text{off})}$	$V_{CC} = 50\text{V}, V_i = 0\text{V}$	-	-	0.5	μA
DC Current Gain	G_i	$V_o = 5\text{V}, I_o = 5\text{mA}$	68	-	-	-
Input Resistor	R_1		7	10	13	k Ω
Resistance ratio	R_2/R_1		3.7	4.7	5.7	-
Gain-Bandwidth Product	f_T	$V_{CE} = 10\text{V}, I_E = 5\text{mA}$ $f = 100\text{MHz}$	-	250	-	MHz

Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 Input Voltage vs Output Current




Fig 2 Output Current vs Input Voltage




Fig 3 DC Current Gain vs Output Current





Fig 4 Output Voltage vs Output Current

Package information (Unit: mm)

SOT-23



Mounting Pad Layout (Unit: mm)

