









LAYOUT: ± 0.05



<i>pin number</i>	<i>pin name</i>
<i>G1</i>	<i>swicth</i>
<i>pin 8</i>	<i>RSV</i>
<i>pin 7</i>	<i>DD</i>
<i>pin 6</i>	<i>VSS</i>
<i>pin 5</i>	<i>SCLK</i>
<i>pin 4</i>	<i>VDD</i>
<i>pin 3</i>	<i>DI</i>
<i>pin 2</i>	<i>CS</i>
<i>pin 1</i>	<i>RSV</i>

-NOTES-

1. Electrical:
Contact resistance: 50m ohms max.
Dielectric withstanding voltage: 500V RMS.
Insulation resistance: 1000M ohms min.
2. Mechanical:
MATE AND UNMATE FORCE:
MATE FORCE: 4.5kg MAX
UNMATE FORCE: 0.5kg MIN
Durability: 1500 cycles MIN.
3. Environment:
Operating Temperature: -25° to +85°.
4. FINISH:
TERMINAL: GOLD Plated Over NICKEL
Contact area, TIN ON
SOLDER TAIL AREA & TIN
Plated All Over NICKEL.
Shell: SPCC WITH NICKEL & GOLD Plated.
5. COLOR:
HOUSING: BLACK.

P/N	DIM-A	DIM-H
HYCW106-TF09-170B	0.70	1.70MM
HYCW106-TF09-150B	0.50	1.50MM



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X: ±2° X.X: ±0.5°				TF短体卡座（带边检测pin）	
		CHECKED BY:	DATE :	PART NO.	HYCW106-TF09-XXXX
		马跃	2014-02-23	MOLD NO.	
UNIT: mm [inch]		APPROVED BY:	DATE :	DRAW NO:	HYC-TF180917413
SCALE:1:1	SIZE: A4	邱国夷	2014-02-23	SHEET NO.	1 OF 1