









REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术指标(Technical Index):

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
5. 绝缘电阻(Insulation resistance): $\geq 500M\Omega$.
6. 耐压: 200V/1 Minute.



序号 (NO.)	零件名称 (Part. Name)	材质 (Material)
①	1.0 掀盖胶芯 (H=2.0) 1.0 Pitch Easy-on Type Housing (H=2.0)	LCP UL94V-0 本色 Natural
②	1.0 掀盖端子 (H=2.0) 1.0 Pitch Easy-on Type Terminal (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating
③	1.0 掀盖后盖 (H=2.0) 1.0 Pitch Easy-on Type Actuator (H=2.0)	LCP UL94V-0 黑色 Black
④	1.0 掀盖焊片 (H=2.0) 1.0 Pitch Easy-on Type Fitting Nail (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating

CUSTOMER DRAWING

DRAWING

CHECKED

APPROVED

TOLERANCES ARE

30-150	±0.35	ANGLE
10-30	±0.2	
5-10	±0.15	
0-5	±0.1	

LAILAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO., LTD

TITLE	FPC连接器1.0间距12PIN翻盖下接H2.0 弯贴	REV.	A
PART NO.	LAIL-FPC-CX01-12P1.0-W	UNITS	mm
DWG. NO.		Projection	