







RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



PIN number variable size comparison table

PART NO	PIN	A	B
HMT-PH2.0-LT2P	2	2.00	8.00
HMT-PH2.0-LT3P	3	4.00	10.00
HMT-PH2.0-LT4P	4	6.00	12.00
HMT-PH2.0-LT5P	5	8.00	14.00
HMT-PH2.0-LT6P	6	10.00	16.00
HMT-PH2.0-LT7P	7	12.00	18.00
HMT-PH2.0-LT8P	8	14.00	20.00
.....			
HMT-PH2.0-LT16P	16	30.00	36.00




NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃



GENERAL TOLERANCES
UNLESS SPECIFIED

X.X ±0.30	X.° ±5°
.XX ±0.20	X.X° ±1°
.XXX ±0.10	X.XX° ±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-PH2.0-LTNP

DESIGN: James
CHED: Talen
APPD: Sophia

TITLE:
WAFER 2.00 立贴

CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1