





2-6Pwith card point
7-24p without card point

Product model	PIN	A	B
HMT-EDGKD-3.81-1-2PGG	2	3.81	8.41
HMT-EDGKD-3.81-1-3PGG	3	7.62	12.22
HMT-EDGKD-3.81-1-4PGG	4	11.43	16.03
HMT-EDGKD-3.81-1-5PGG	5	15.24	19.84
HMT-EDGKD-3.81-1-6PGG	6	19.05	23.65
HMT-EDGKD-3.81-1-7PGG	7	22.86	27.46
.....			
HMT-EDGKD-3.81-1-24PGG	24	3.81x(N-1)	3.81x(N-1)+4.6

UL Standard	B	C	D
Rated Voltage (V)/Current (A)	300/8	300/8	300/8
IEC Standard			
Overvoltage Category/Pollution Degree	III /3	III /2	II /3
Rated Voltage (V)/Current (A)	/	/	250/12
Rate Impulse Voltage (KV)	/	/	2.5
Wire Range(rigid and flexible) (mm ² /AWG)	0.2 ¹ .5/28~16		
Pitch(mm)/Poles	3.81/N=02~24P		
Stripping length(mm)	9		
Operating temperature(° C)	-40C° ~+105C°		
Conform to RoHS	Yes		

5	Spring	Stainless steel	/
4	Clamp	Copper Alloy	Sn Plated
3	Button	POM	UL94HB
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
		PART NO. HMT-EDGKD-3.81-1-NPGG	TITLE: Socket-type terminal
		DESIGN: James	CUSTOMER
		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
MANUFACTURE DWG			SCALE N:A
			SHEET 1/1