

Super Fast Recovery Surface Mounted Rectifiers

Reverse Voltage - 50 to 600 V


Forward Current - 6.0 A

FEATURES

- ◆The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆Idea for printed circuit board
- ◆Glass passivated Junction chip
- ◆Low reverse leakage
- ◆High forward surge current capability
- ◆High temperature soldering guaranteed 260°C/10 seconds at terminals

MECHANICAL DATA

- ◆Case : TO-277
- ◆Terminals : Solder plated, solderable per MIL-STD-750,Method 2026
- ◆Polarity : Polarity symbol marking on body
- ◆Mounting Position : Any
- ◆Weight : 0.003 ounce, 0.092 grams



Absolute Maximum Ratings and Electrical characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	Symbols	ES6ASP	ES6BSP	ES6CSP	ES6DSP	ES6FSP	ES6GSP	ES6JSP	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	50	100	150	200	300	400	600	V
Maximum RMS voltage	V_{RMS}	35	70	105	140	210	280	420	V
Maximum DC Blocking Voltage	V_{DC}	50	100	150	200	300	400	600	V
Maximum Average Forward Rectified Current at T _L =100°C	I_(AV)	6.0							A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed On Rated Load	I_{FSM}	150							A
Maximum Instantaneous Forward Voltage at 6.0A	V_F	0.95				1.3		1.7	V
Maximum Instantaneous Reverse Current at Rated DC Reverse Voltage T _A = 25°C T _A = 125°C	I_R	2.0 200							uA
Maxinum reverse recovery time(Note 1)	T_{rr}	35							ns
Typical junction capacitance (Note2)	C_J	82.0							pF
Typical Thermal Resistance	R_{qJA}	60							°C/W
Operating junction and storage temperature range	T_j, T_{stg}	-55 ~ +150							°C

Note:

- 1.Reverse recovery time test condition: $I_F=0.5A$ $I_R=1.0A$ $I_{rr}=0.25A$
- 2.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

Ratings And Characteristic Curves

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS






FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS



Marking Diagram



Ordering information


Package	Packing Description	Packing Quantity
TO-277	Tape/Reel, 13"reel	5000PCS/Reel 50000PCS/Cartron

Package Dimensions

TO-277

Dim.	Millimeter(mm)		mil	
	Min.	Max.	Min.	Max.
A	1.1	1.2	43	47
A2	0.3	0.4	12	16
b1	0.8	1	32	39
b2	1.7	1.9	67	75
D	3.9	4.1	154	162
D1	3.054		120	
E	6.4	6.6	252	260
e	1.84		73	
E1	5.3	5.5	209	217
E2	3.549		140	
L	0.8	1	32	39
L1	0.5	0.7	20	28
W	1.1	1.4	43	55

The recommended mounting pad size



Disclaimer

The information presented in this document is for reference only. Guangdong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.