

Transient Voltage Suppressor

FEATURES

- ◆ 2000Watts peak pulse power ($t_p = 8/20\mu s$)
- ◆ Solid-state silicon-avalanche technology
- ◆ Low clamping voltage
- ◆ Low leakage current
- ◆ Protection one data/power line
- ◆ IEC 61000-4-2 $\pm 30kV$ contact $\pm 30kV$ air
- ◆ IEC 61000-4-4 (EFT) 40A (5/50ns)
- ◆ IEC 61000-4-5 (Lightning) 130A (8/20 μs)

APPLICATIONS

- ◆ Cell Phone Handsets and Accessories
- ◆ Microprocessor based equipment
- ◆ Personal Digital Assistants (PDA's)
- ◆ Notebooks, Desktops, and Servers
- ◆ Portable Instrumentation

MECHANICAL DATA

- ◆ DFN1610-2L package
- ◆ Molding compound flammability rating: UL 94V-0
- ◆ Packaging: Tape and Reel
- ◆ RoHS/WEEE Compliant




DFN1610-2L

Marking Code

ESD1610D5V0	5W*
-------------	-----

Schematic & PIN Configuration




Absolute Maximum Rating

Rating	Symbol	Value	Units
Peak Pulse Power ($t_p = 8/20\mu s$)	P_{PP}	2000	W
Maximum Peak Pulse Current ($t_p = 8/20\mu s$)	I_{PP}	130	A
Operating Temperature	T_j	-55 to +125	°C
Storage Temperature	T_{stg}	-55 to +150	°C

Electrical Parameters (T=25°C)


Symbol	Parameter
I_{PP}	Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Reverse Stand-Off Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F




Electrical Characteristics

Parameter	Conditions	Symbol	Min	Typ	Max	Units
Reverse Stand-Off Voltage		V_{RWM}			5	V
Reverse Breakdown Voltage	$I_T=1mA$	V_{BR}	6		7.5	V
Reverse Leakage Current	$V_{RWM}=5V$	I_R			1	μA
Peak Pulse Current	$t_p=8/20\mu s$	I_{PP}		130		A
Clamping Voltage	$I_{PP}=130A, t_p=8/20\mu s$	V_C		16		V
Junction Capacitance	$V_R=0V, f=1MHz$	C_j		800		pF


Typical Characteristics




Non-repetitive peak pulse power vs. Pulse time




Power derating vs. Ambient temperature




Clamping voltage vs. Peak pulse current



Capacitance vs. Reverse voltage



8/20μs waveform per IEC61000-4-5



Contact discharge current waveform per IEC61000-4-2

Ordering information


Package	Packing Description	Packing Quantity
DFN1610-2L	Tape/Reel, 7" reel	3000PCS/Reel 120000PCS/Carton

Package Dimensions

DFN1610-2L

Dim.	Millimeter(mm)		Inches	
	Min.	Max.	Min.	Max.
A	0.50	0.60	0.020	0.024
A1	-	0.05	-	0.002
D	1.50	1.70	0.060	0.067
E	0.90	1.10	0.035	0.043
e	Typ1.05		Typ0.041	
b	0.35	0.45	0.014	0.018
L	0.75	0.95	0.030	0.037

The recommended mounting pad size



Dim.	Millimeter(mm)
	TYP
X	0.62
Y	1.00
P	1.20

Disclaimer

The information presented in this document is for reference only. Guangdong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.