



TCXO UNIT WITH HCMOS OUTPUT IN SMD 5.0x3.2MM PLASTIC PACKAGE.

PRODUCT FEATURES

- Small dimensions 5.0x3.2x1.6 with 6 solder pads.
- Tight stabilities over temperature range.
- RoHS compliant, LEAD-FREE, HALOGEN-FREE and REACH compliant.

APPLICATIONS

- WiMAX / WLAN / Ethernet
- Mobil applications
- Telecommunication

PRODUCT PHOTO (NOT IN SCALE)




PRODUCT SPECIFICATIONS

PARAMETER	SUPPLY VOLTAGE 3.3/ 5.0V			REMARKS
Frequency range	10 ~ 52MHz			--
Frequency tolerance	$\pm 2.0\text{ppm}$			Initial tol. @+25°C
Frequency stability	$\pm 0.05\text{ppm} / \pm 0.1; / \pm 0.14\text{ppm}; \pm 0.28\text{ppm}$			See note below table
Operating temperature range	-30 to +85°C / -40 to +85°C / -55 to +85°C			In combination to above stabilities.
Aging per year	$\pm 1.0\text{ppm}$			@+25°C
Output waveform and load	LVCMOS 15pF			--
Output voltage level HIGH	90%Vcc			Minimum
Output voltage level LOW	10%Vcc			Maximum
Rise and Fall times	5ns	6ns	8ns	@10~90% of Vcc
Symmetry (duty cycle)	45~55%			@ 50%Vcc
Phase noise (example 19.2MHz)	-115dBc/Hz / -135dBc/Hz / -148dBc/Hz			@100Hz / 1kHz / 10kHz
Phase jitter RMS	<1ps			12kHz $\leq$ Fj $\leq$ 20MHz
Supply current	7mA			@15pF

Note: Frequency stability is the frequency deviation over temperature range in reference to +25°C

PACKAGE OUTLINE / DIMENSIONS



PACKAGING INFORMATION

- Tape & Reel compliant to EIA-481.
- Embossed carrier width 12mm.
- Component pitch in carrier 8mm.
- Reel diameter 180mm.
- QTY per reel: 1,000pcs

RECOMMENDED REFLOW PROFILE

