

QUARTZ CRYSTAL UNIT IN SMD 5.0x3.2MM GLASS SEAL PACKAGE.
PRODUCT FEATURES

- Dimensions 5.0x3.2x1.3 with 2 solder pads.
- Low cost ceramic glass seal package.
- Tight tolerances and stabilities over temperature range.
- RoHS compliant by exemption and HALOGEN-FREE.


PRODUCT PHOTO (NOT IN SCALE)

APPLICATIONS

- Motherboard
- Computer peripherals
- Handheld equipment

PRODUCT SPECIFICATIONS

PARAMETER	0153G2		CONDITIONS / REMARKS
Nominal frequency range	8.0 ~ 80.0MHZ		Fundamental up to 50MHZ and 3rd overtone from 40MHZ.
Crystal cut and mode	AT-cut / FUND & 3rd Overtone		
Frequency tolerance	±10ppm to ±50ppm		other options available.
Frequency stability	±10ppm	±30ppm	other options available.
Operating temperature range	-20 to +70℃	-40 to +85℃	other options available.
Equivalent series resistance	80Ω		FUND – 8.0 ~ 12.0MHZ
	60Ω		FUND – 12.1 ~ 20.0MHZ
	50Ω		FUND – 20.1 ~ 50.0MHZ
	120Ω		3rd OT – 40.0 ~ 60.0MHZ
	100Ω		3rd OT – 60.1 ~ 80.0MHZ
Load capacitance	6 ~ 32pF or SERIES		Please specify.
Shunt capacitance	<5pF		--
Drive level	10μW TYP / 200μW MAX		--
Aging	±3ppm		Per year

PACKAGE OUTLINE / DIMENSIONS

PACKAGING INFORMATION

- Tape & Reel compliant to EIA-481.
- Embossed carrier width 12mm.
- Component pitch in carrier 8mm.
- Reel diameter 180mm.
- QTY per reel: 1,000pcs MAX.

RECOMMENDED REFLOW PROFILE
