






未注公差/General tolerances(mm)

0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50



REV	ECN	DESCRIPTION	DRFT	DATE



PCB Layout

DB2ERM — 5.08 — XXP — C
(Series No.) (Pitch) (Poles)

(Color):GN:(Green), BK:(Black), BU:(Blue), RD:(Red), GY:(Gray)
OG:(Orange), WT:(White), YL:(Yellow), CR:(Clear)

UL 标准/UL Standard:	B	C	D
额定电压/电流/Rated Voltage(V)/Current(A)	300/15	/	300/10
IEC 标准/IEC Standard:			
过压类别/Overvoltage Category/ 污染等级/Pollution Degree	III/3	III/2	II/3
额定电压/电流/Rated Voltage(V)/Current(A)	250/15	320/15	630/15
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	4.0	4.0	4.0
螺丝扭矩/Torque Tightening(N·m/Lb.in)	/		
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm ² /AWG)	/		
间距/Pitch(mm)/线数范围/Poles	5.08/02~24		
剥线长度/Stripping length(mm)	/		
使用温度范围/Operating temperature(°C)	-40~+105		
符合RoHS环保要求/Conform to RoHS	Yes		

Nut	Copper alloy	
Pin header	Copper alloy	Sn Plated
Housing	PA66	UL94V-0
NAME OF PART	MATERIAL	NOTES

MAT NO.: /	宁波地博电气有限公司 NINGBO DORABO ELECTRICAL CO., LTD		
STATUS: /			
APPD: JTING Chen 2025.07.10	NAME: DB2ERM-5.08-XXP-C		
CHKD: Duck Mao 2025.07.10			
DRFT: Steven Lu 2025.07.10	DRAWING NO.: /		REV M1
SIZE: A4	mm (inch)	TYPE: CUSTOMER_DRAWING	SCALE: 1:1 SHEET 1/1