

## VOLTAGE RANGE

20 to 60 Volts

## CURRENT



3.0 Ampere

## FEATURES

- \* Ideal for surface mount applications
- \* Easy pick and place
- \* Built-in strain relief
- \* Low forward voltage drop

## MECHANICAL DATA

- \* Case: Molded plastic
- \* Epoxy: UL 94V-0 rate flame retardant
- \* Terminals: Solder plated, solderable per MIL-STD-202F method 208 guaranteed
- \* Polarity: Color band denotes cathode end
- \* Mounting position: Any
- \* Weight: 0.063 gram



## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwise specified.  
Single phase half wave, 60Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.

| TYPE NUMBER                                                                                        | SK32A      | SK33A | SK34A | SK35A | SK36A | UNITS |
|----------------------------------------------------------------------------------------------------|------------|-------|-------|-------|-------|-------|
| Maximum Recurrent Peak Reverse Voltage                                                             | 20         | 30    | 40    | 50    | 60    | V     |
| Maximum RMS Voltage                                                                                | 14         | 21    | 28    | 35    | 42    | V     |
| Maximum DC Blocking Voltage                                                                        | 20         | 30    | 40    | 50    | 60    | V     |
| Maximum Average Forward Rectified Current                                                          |            |       |       |       |       |       |
| See Fig. 1                                                                                         | 3.0        |       |       |       |       | A     |
| Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method) | 80         |       |       |       |       | A     |
| Maximum Instantaneous Forward Voltage at 3.0A                                                      | 0.55       |       |       | 0.70  |       | V     |
| Maximum DC Reverse Current Ta=25°C                                                                 | 0.1        |       |       |       |       | mA    |
| at Rated DC Blocking Voltage Ta=100°C                                                              | 5          |       |       |       |       | mA    |
| Typical Junction Capacitance (Note1)                                                               | 300        |       |       |       |       | pF    |
| Typical Thermal Resistance R JA (Note 2)                                                           | 75         |       |       |       |       | °C/W  |
| Operating Temperature Range Tj                                                                     | -65 — +150 |       |       |       |       | °C    |
| Storage Temperature Range Tstg                                                                     | -65 — +150 |       |       |       |       | °C    |

### NOTES:

1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
2. Thermal Resistance Junction to Ambient.

## RATING AND CHARACTERISTIC CURVES

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL FORWARD CHARACTERISTICS




FIG.3 - TYPICAL REVERSE CHARACTERISTICS




FIG.4-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT






FIG.5-TYPICAL JUNCTION CAPACITANCE




## Soldering parameters

| Reflow Condition                                        |                                   | Pb-Free assembly<br>(see as below) |
|---------------------------------------------------------|-----------------------------------|------------------------------------|
| Pre Heat                                                | -Temperature Min ( $T_{s(min)}$ ) | +150 °C                            |
|                                                         | -Temperature Max( $T_{s(max)}$ )  | +200 °C                            |
|                                                         | -Time (Min to Max) (ts)           | 60-180 secs.                       |
| Average ramp up rate (Liquid us Temp ( $T_L$ ) to peak) |                                   | 3 °C/sec. Max                      |
| $T_{s(max)}$ to $T_L$ - Ramp-up Rate                    |                                   | 3 °C/sec. Max                      |
| Reflow                                                  | -Temperature( $T_L$ )(Liquid us)  | +217 °C                            |
|                                                         | -Temperature( $t_L$ )             | 60-150 secs.                       |
| Peak Temp ( $T_P$ )                                     |                                   | +260(+0/-5) °C                     |
| Time within 5 °C of actual Peak Temp ( $t_p$ )          |                                   | 30 secs. Max                       |
| Ramp-down Rate                                          |                                   | 6 °C/sec. Max                      |
| Time 25 °C to Peak Temp ( $T_P$ )                       |                                   | 8 min. Max                         |
| Do not exceed                                           |                                   | +260 °C                            |




## Package Dimensions & Suggested Pad Layout

### SMA






| SMA                  |      |      |
|----------------------|------|------|
| Dim                  | Min  | Max  |
| A                    | 2.40 | 2.79 |
| B                    | 3.99 | 4.50 |
| C                    | 1.32 | 1.47 |
| D                    | -    | 0.20 |
| E                    | 4.93 | 5.28 |
| G                    | 0.15 | 0.31 |
| H                    | 0.76 | 1.52 |
| J                    | 1.98 | 2.29 |
| All Dimensions in mm |      |      |



| Dimensions | Value (in mm) |
|------------|---------------|
| C          | 4.20          |
| G          | 1.90          |
| X          | 2.30          |
| X1         | 6.50          |
| Y          | 2.00          |

## Tape & reel specification

| Tape                                                                                |  | Symbol            | Dimension (mm) |
|-------------------------------------------------------------------------------------|--|-------------------|----------------|
|    |  | P0                | 4.00±0.20      |
|                                                                                     |  | P1                | 4.00±0.20      |
|                                                                                     |  | P2                | 2.00±0.20      |
|                                                                                     |  | D0                | 1.60±0.20      |
|                                                                                     |  | D1                | 1.60±0.20      |
|                                                                                     |  | E                 | 1.75±0.20      |
|                                                                                     |  | F                 | 5.50±0.15      |
|                                                                                     |  | W                 | 12.00±0.25     |
|                                                                                     |  | A0                | 2.75±0.20      |
|                                                                                     |  | B0                | 5.25±0.20      |
|                                                                                     |  | K0                | 2.45±0.25      |
|                                                                                     |  | T                 | 0.20±0.10      |
| 7" Reel                                                                             |  | D2                | 176.0±5.0      |
|   |  | D3                | 55.0Min.       |
|                                                                                     |  | D4                | 14.0±2.5       |
|                                                                                     |  | W1                | 14.0±2.5       |
|                                                                                     |  | Quantity: 2000PCS |                |
| 13" Reel                                                                            |  | D5                | 330.0±5.0      |
|  |  | D6                | 73.0Min.       |
|                                                                                     |  | D7                | 14.0±2.5       |
|                                                                                     |  | W2                | 14.0±2.5       |
|                                                                                     |  | Quantity: 5000PCS |                |