





		1		2		3		4		5																																																																																																							
A						规格参数 1、额定电流：1A AC，DC 2、额定电压：50V AC，DC 3、工作温度：-25℃~+85℃ 4、接触电阻：20mΩ Max 5、绝缘电阻：100MΩ Min 6、耐电压：500V AC/minute 7、材质： 塑胶 PA66,阻燃等级：UL94V-0		A																																																																																																									
B						<table><tr><th rowspan="2">PIN</th><th colspan="4">尺寸 (mm)</th></tr><tr><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>-02Y</td><td>1.00</td><td>5.00</td><td>2.40</td><td>2.60</td></tr><tr><td>-03Y</td><td>2.00</td><td>6.00</td><td>3.40</td><td>3.80</td></tr><tr><td>-04Y</td><td>3.00</td><td>7.00</td><td>4.40</td><td>4.60</td></tr><tr><td>-05Y</td><td>4.00</td><td>8.00</td><td>5.40</td><td>4.60</td></tr><tr><td>-06Y</td><td>5.00</td><td>9.00</td><td>6.40</td><td>4.60</td></tr><tr><td>-07Y</td><td>6.00</td><td>10.00</td><td>7.40</td><td>4.60</td></tr><tr><td>-08Y</td><td>7.00</td><td>11.00</td><td>8.40</td><td>6.60</td></tr><tr><td>-09Y</td><td>8.00</td><td>12.00</td><td>9.40</td><td>6.60</td></tr><tr><td>-10Y</td><td>9.00</td><td>13.00</td><td>10.40</td><td>6.60</td></tr><tr><td>-11Y</td><td>10.00</td><td>14.00</td><td>11.40</td><td>6.60</td></tr><tr><td>-12Y</td><td>11.00</td><td>15.00</td><td>12.40</td><td>6.60</td></tr><tr><td>-13Y</td><td>12.00</td><td>16.00</td><td>13.40</td><td>6.60</td></tr><tr><td>-14Y</td><td>13.00</td><td>17.00</td><td>14.40</td><td>6.60</td></tr><tr><td>-15Y</td><td>14.00</td><td>18.00</td><td>15.40</td><td>6.60</td></tr><tr><td>-16Y</td><td>15.00</td><td>19.00</td><td>16.40</td><td>6.60</td></tr><tr><td>-17Y</td><td>16.00</td><td>20.00</td><td>17.40</td><td>6.60</td></tr><tr><td>-18Y</td><td>17.00</td><td>21.00</td><td>18.40</td><td>6.60</td></tr><tr><td>-19Y</td><td>18.00</td><td>22.00</td><td>19.40</td><td>6.60</td></tr><tr><td>-20Y</td><td>19.00</td><td>23.00</td><td>20.40</td><td>6.60</td></tr></table>		PIN	尺寸 (mm)				A	B	C	D	-02Y	1.00	5.00	2.40	2.60	-03Y	2.00	6.00	3.40	3.80	-04Y	3.00	7.00	4.40	4.60	-05Y	4.00	8.00	5.40	4.60	-06Y	5.00	9.00	6.40	4.60	-07Y	6.00	10.00	7.40	4.60	-08Y	7.00	11.00	8.40	6.60	-09Y	8.00	12.00	9.40	6.60	-10Y	9.00	13.00	10.40	6.60	-11Y	10.00	14.00	11.40	6.60	-12Y	11.00	15.00	12.40	6.60	-13Y	12.00	16.00	13.40	6.60	-14Y	13.00	17.00	14.40	6.60	-15Y	14.00	18.00	15.40	6.60	-16Y	15.00	19.00	16.40	6.60	-17Y	16.00	20.00	17.40	6.60	-18Y	17.00	21.00	18.40	6.60	-19Y	18.00	22.00	19.40	6.60	-20Y	19.00	23.00	20.40	6.60	B	
PIN	尺寸 (mm)																																																																																																																
	A	B	C	D																																																																																																													
-02Y	1.00	5.00	2.40	2.60																																																																																																													
-03Y	2.00	6.00	3.40	3.80																																																																																																													
-04Y	3.00	7.00	4.40	4.60																																																																																																													
-05Y	4.00	8.00	5.40	4.60																																																																																																													
-06Y	5.00	9.00	6.40	4.60																																																																																																													
-07Y	6.00	10.00	7.40	4.60																																																																																																													
-08Y	7.00	11.00	8.40	6.60																																																																																																													
-09Y	8.00	12.00	9.40	6.60																																																																																																													
-10Y	9.00	13.00	10.40	6.60																																																																																																													
-11Y	10.00	14.00	11.40	6.60																																																																																																													
-12Y	11.00	15.00	12.40	6.60																																																																																																													
-13Y	12.00	16.00	13.40	6.60																																																																																																													
-14Y	13.00	17.00	14.40	6.60																																																																																																													
-15Y	14.00	18.00	15.40	6.60																																																																																																													
-16Y	15.00	19.00	16.40	6.60																																																																																																													
-17Y	16.00	20.00	17.40	6.60																																																																																																													
-18Y	17.00	21.00	18.40	6.60																																																																																																													
-19Y	18.00	22.00	19.40	6.60																																																																																																													
-20Y	19.00	23.00	20.40	6.60																																																																																																													
C								C																																																																																																									
更改记录		标记	变更内容	签名/日期	未注公差	单位	mm	标准化	签名/日期	品名	1.0单排带钩孔座 1.0普通带扣-NY																																																																																																						
					X.X ±0.30	版本	A	编制	周少华 2022.08.20	料号	ZJLQ-SH1.0A10002-NY																																																																																																						
					X.XX ±0.20	比例	1:1	审核	赵先礼 2022.08.20	浙江领强电子科技有限公司																																																																																																							
					X.XXX ±0.10	投影		批准	田泽民 2022.08.20																																																																																																								
					Angle ±3.0°	页次	1/1																																																																																																										
		1		2		3		4		5																																																																																																							