




RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE: ± 0.05)

RECOMMENDED METAL MASK T=0.12mm


- RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE: ± 0.05)
RECOMMENDED METAL MASK T=0.12mm
- SMT SOLDER AREA
 - NO PATTERN AND VIA HOLE IN HTIS AREA

SIM CARD


Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O

PART INSTRUCTIONS:


PART NUMBER	DESCRIPTION
HMT-SMN-305-6PH15	6PIN
HMT-SMN-305-7PH15	6+1PIN




STEP 1 INSERT Micro-SIM CARD



STEP 2 PUSH THE SHELL



STEP 3 FINISH



GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	± 0.30	X.°	$\pm 5^\circ$
.XX	± 0.20	X.X°	$\pm 1^\circ$
.XXX	± 0.10	X.XX°	$\pm 0.5^\circ$

MANUFACTURE DWG






深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.	HMT-SMN-305-6PH15
DESIGN:	James
CHED:	Talen
APPD:	Sophia

TITLE: 1.5H 6PIN HINGE NANO SIM CARD CONNECTOR		
CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/2

RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



NOTES:

1. 15 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE ± 0.2 .
2. MATERIAL: CLARITY CONDUCTIVE POLYSTYRENE ALLOY
100% RECYCLABLE.
3. ALL DIMENSIONS MEET EIA-481-3 REQUIREMENTS.
4. THICKNESS: $0.30 \pm 0.05\text{MM}$
5. COMPONENT LOAD PER 30.6M" REEL: 1500PCS.
6. 10REEL/CARTON: 15000pcs

GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ± 0.30	X. $^\circ$ $\pm 5^\circ$	PART NO. HMT-SMN-305-6PH15	TITLE: 1.5H 6PIN HINGE NANO SIM CARD CONNECTOR	
.XX ± 0.20	X.X $^\circ$ $\pm 1^\circ$	DESIGN: James	CUSTOMER	SIZE A4
.XXX ± 0.10	X.XX $^\circ$ $\pm 0.5^\circ$	CHED: Talen		UNITS MM
MANUFACTURE DWG		APPD: Sophia		SCALE N:A
				SHEET 2/2