














NOTE :

1 - FOR CRMP SPECIFICATION , SEE : FE CS 06 005

2 - FOR PACKAGING , SEE : PU N°076

3\_ ( ) NO TOLERANCED DIMENSIONS, GIVEN FOR INFORMATION

| Etat / State |                          | Références                                                                                                |                 |                 |                 | Material        | Classe |
|--------------|--------------------------|-----------------------------------------------------------------------------------------------------------|-----------------|-----------------|-----------------|-----------------|--------|
| GTS 1        | Pré-établé<br>Pre-finned | MVL P/N                                                                                                   | PP10001619      | PP10000489      | PP10000490      | Cu Ni 3 Si 1 Mg | 125°   |
|              |                          | REVISION                                                                                                  | A               | A               | A               |                 |        |
|              |                          | DELPHI P/N                                                                                                | 13955989        | 13648598        | 13768627        |                 |        |
|              |                          | REVISION                                                                                                  | 01              | 01              | 01              |                 |        |
| GTS 3        |                          | MVL P/N                                                                                                   | 260 CC 1 S 0120 | 260 CC 1 S 1120 | 260 CC 1 S 2120 |                 |        |
|              |                          | REVISION                                                                                                  | A               | A               | A               |                 |        |
|              |                          | DELPHI P/N                                                                                                | 33500712        | 33502051        | 33500713        |                 |        |
|              |                          | REVISION                                                                                                  | 01              | 01              | 01              |                 |        |
|              |                          | Section / Gauge                                                                                           | 0.22 to 0.35    | 0.5             | 0.75 to 1       |                 |        |
|              |                          |  Isolant<br>Insulation | 1.2 to 1.5      | 1.4 to 1.7      | 1.6 to 1.9      |                 |        |
|              |                          | A                                                                                                         | 1.49            | 1.82            | 2.24            |                 |        |
|              |                          | B                                                                                                         | 1.64            | 2.04            | 2.37            |                 |        |
|              |                          | C                                                                                                         | 0.3             | 0.4             | 0.6             |                 |        |
|              |                          | D ± 0.3                                                                                                   | 2.82            | 2.94            | 3.3             |                 |        |
|              |                          | E                                                                                                         | 2.67            | 2.96            | 3.5             |                 |        |
|              |                          | F                                                                                                         | 0.85            | 0.85            | 0.85            |                 |        |
|              |                          | G ± 0.10                                                                                                  | 5.10            | 5.10            | 4.85            |                 |        |
|              |                          | H                                                                                                         | 3.0             | 3.0             | 3.5             |                 |        |

[illegible]