





P/N	CKT	A	B	C
HMT-PHB2.0-4P-WT	2*2	2.00	6.00	3.20
HMT-PHB2.0-6P-WT	2*3	4.00	8.00	3.20
HMT-PHB2.0-8P-WT	2*4	6.00	10.00	3.00
HMT-PHB2.0-10P-WT	2*5	8.00	12.00	5.00
HMT-PHB2.0-12P-WT	2*6	10.00	14.00	7.00
HMT-PHB2.0-14P-WT	2*7	12.00	16.00	9.00
HMT-PHB2.0-16P-WT	2*8	14.00	18.00	11.00
HMT-PHB2.0-18P-WT	2*9	16.00	20.00	13.00
HMT-PHB2.0-20P-WT	2*10	18.00	22.00	15.00
HMT-PHB2.0-22P-WT	2*11	20.00	24.00	17.00
HMT-PHB2.0-24P-WT	2*12	22.00	26.00	19.00
HMT-PHB2.0-26P-WT	2*13	24.00	28.00	21.00
HMT-PHB2.0-28P-WT	2*14	26.00	3.00	23.00
HMT-PHB2.0-30P-WT	2*15	28.00	32.00	25.00
HMT-PHB2.0-32P-WT	2*16	30.00	34.00	27.00
HMT-PHB2.0-36P-WT	2*18	34.00	38.00	31.00
HMT-PHB2.0-40P-WT	2*20	38.00	42.00	35.00
HMT-PHB2.0-44P-WT	2*22	42.00	46.00	39.00



适用线路板 (PCB LAYOUT)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$.
3. 适用线规: AWG#28~#22.
4. 额定电压: 250V DC/AC(rms).
5. 额定电流: 3.0A AC, DC.
6. 接触电阻: $\leq 20\text{m}\Omega$.
7. 耐压值: 800V AC/minute.
8. 绝缘电阻: $\geq 1000\text{M}\Omega$.

1	2.0A 型双排立式 WTB胶芯	LCP UL94V-0 本色
2	2.0A 型双排卧式 短端子	铜合金/表面镀锡
3	2.0A 型双排卧式 长端子	铜合金/表面镀锡
序号	名称	材质

GENERAL TOLERANCES UNLESS SPECIFIED		HMTconn 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.±0.50	X.°±1°	PART NO. HMT-PHB2.0-NP-WT	TITLE: 2.0 Pitch A型双排卧式WTB
.X±0.20		DESIGN: James	CUSTOMER
.XX±0.10		CHED: Talen	SIZE A4
MANUFACTURE DWG		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1