






开关安装面板
(Switch panel hole dim.)



Screw selection:
螺杆选择:

Screw type 螺杆类型	Threaded 有螺纹	No threaded 无螺纹
Diagram 简图		

Function choice:
功能选择:

N0.	specification 产品规格	function 功能
01	MTS102	SPDT: ON - ON
02	MTS112	SPDT: ON - (ON)
03	MTS103	SPDT: ON- OFF -ON
04	MTS113	SPDT: (ON)-OFF- ON
05	MTS123	SPDT: (ON)-OFF- (ON)

Specification(技术要求):

- Rated Load(额定负载): 2A 250VAC; 5A 125VAC
- Temperature Range(操作温度): -25℃~+85℃
- Contact Resistance(接触电阻): ≤0.02 Ω
- Insulation Resistance(绝缘电阻): ≥1000M Ω
- Withstand Voltage(耐压): AC1500V/min
- Operating Force(操作力): 2--15N
- Life(寿命): 50000 times
- material(材料): 胶木 和 Cu/Ep Ag(黄铜镀银)

01	--	第一次出图			2024.08.26
版次 (REV.)	参考 (REF.)	描述(DESCRIPTION)		绘图 (DRAW BY)	批核 (APP. BY)
名称 (NAME)	Toggle Switch Specifications(钮子开关规格书)		功能 (Function) See above(见上述)		
型号 (MODEL NO.)	MTS Series CAX-MTS1**C3-YB-10.8JL		绘图 (DRAW BY)	批核 (APP. BY)	
物料编号 (Material No.)	MTS102C3	比例 (SCALE) NTS(见标注)	日期 (DATE) 2024.08.26	日期 (DATE)	
公差除特别要求外, 均按此规定执行: X.=±0.20, .X=±0.15, .XX=±0.1, <=±1°, 单位:mm (Tolerance unless otherwise specified: X.=±0.20, .X=±0.15, .XX=±0.10, <=±1°, unit:mm)					

浙江创都电子科技有限公司