




PIN number variable size comparison table				
PART NO	Pin	A	B	C
HMT-GH1. 25-LT2P	2	1. 25	5. 75	3. 75
HMT-GH1. 25-LT3P	3	2. 50	7. 00	5. 00
HMT-GH1. 25-LT4P	4	3. 75	8. 25	6. 25
HMT-GH1. 25-LT5P	5	5. 00	9. 50	7. 50
HMT-GH1. 25-LT6P	6	6. 25	10. 75	8. 75
.....				
HMT-GH1. 25-LT16P	16	18. 75	23. 25	21. 25

1. *BASE: LCP*
2. *PIN: Brass*
3. *Solder Tab: Brass*

1. Spacing: 1.25
2. Voltage Rating: 125V AC DC
3. Current Rating: 1A AC, DC
4. Insulation Resistance: 100M Ω Min
5. Contact Resistance: 20m Ω Max
6. Withstanding voltage: 500V AC 1/Minute
7. Temperatuer Range: -25 $^{\circ}$ C ~+ 85 $^{\circ}$ C



GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMT CONN <i>Shenzhen Huamingtong Electronics Co., Ltd</i>			
X.X ±0.30	X.° ±5°	PART NO.	TITLE:		
.XX ±0.20	X.X° ±1°	HMT-GH1.25-LTNP	WAFER GH1.25 立贴带扣		
.XXX ±0.10	X.XX° ±0.5°	DESIGN: <i>James</i>	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: <i>Talen</i>		SCALE	SHEET
		APPD: <i>Sophia</i>		N:A	1/1