





- 技术指标:
- 1. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
 - 2. 额定电压: 250V AC, DC.
 - 3. 耐电压: 800V AC/minute.
 - 4. 接触电阻: $\leq 20\text{m}\Omega$.
 - 5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
 - 6. 额定电流: 3A AC, DC.
- 材料:
- 1. 塑胶: PA66 白色

型号	CKT	A	B
HMT-PHD2. 0-4P-JK-A1	2*2	2.00	6.00
HMT-PHD2. 0-6P-JK-A1	2*3	4.00	8.00
HMT-PHD2. 0-8P-JK-A1	2*4	6.00	10.00
HMT-PHD2. 0-10P-JK-A1	2*5	8.00	12.00
HMT-PHD2. 0-12P-JK-A1	2*6	10.00	14.00
HMT-PHD2. 0-14P-JK-A1	2*7	12.00	16.00
HMT-PHD2. 0-16P-JK-A1	2*8	14.00	18.00
HMT-PHD2. 0-18P-JK-A1	2*9	16.00	20.00
HMT-PHD2. 0-20P-JK-A1	2*10	18.00	22.00
HMT-PHD2. 0-22P-JK-A1	2*11	20.00	24.00
HMT-PHD2. 0-24P-JK-A1	2*12	22.00	26.00
HMT-PHD2. 0-26P-JK-A1	2*13	24.00	28.00
HMT-PHD2. 0-28P-JK-A1	2*14	26.00	30.00
HMT-PHD2. 0-30P-JK-A1	2*15	28.00	32.00
HMT-PHD2. 0-32P-JK-A1	2*16	30.00	34.00
HMT-PHD2. 0-34P-JK-A1	2*17	32.00	36.00
HMT-PHD2. 0-36P-JK-A1	2*18	34.00	38.00
HMT-PHD2. 0-38P-JK-A1	2*19	36.00	40.00
HMT-PHD2. 0-40P-JK-A1	2*20	38.00	42.00

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	X.°±5°	PART NO.	TITLE:	
.XX±0.25	.X°±1°	HMT-PHD2.0-NP-JK-A1	PHD2.0公头胶壳	
.XXX±0.15		DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		A4
				MM
			SCALE	SHEET
			N:A	1/1