


MS30N95HGC0


Features

- $V_{DS}=950V, I_D=30A$
- $R_{DS(on), type}=0.25\Omega @15A$
- avalanche tested and current rated
- Fast intrinsic Rectifier



Applications

- High power density
- Easy to mount
- Space savings



Absolute Ratings ($T_c=25^\circ C$)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DSS}	950	V
Transient Gate-Source Voltage	V_{GSM}	± 30	V
Continuous Gate-Source Voltage	V_{GSS}	± 20	V
Drain Current-continuous	I_D	30	A
Drain Current-pulse(note1)	I_{DM}	55	A
Single Pulsed Avalanche Energy(note2)	E_{AS}	750	mJ
Maximum Power Dissipation	P_D	290	W
Operating and Storage Temperature Range	T_J, T_{STG}	$-55 \sim +150$	$^\circ C$
Maximum lead temperature for soldering purposes	T_L	300	$^\circ C$
Isolation Voltage Between Case to Thermal	V_{ISO}	3.0	kV

Electrical Characteristics($T_{CASE}=25^\circ C$ unless otherwise specified)

Parameter	Symbol	Tests conditions	Min	Typ	Max	Units
-----------	--------	------------------	-----	-----	-----	-------

Drain-Source Voltage	BV _{DSS}	I _D =3mA, V _{GS} =0V	950	-	-	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =V _{DSS} , V _{GS} =0V	-	-	1	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V, V _{DS} =0V	-	-	±100	nA
On-Characteristics						
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =2.5mA	3.0	-	5.0	V
Static Drain-Source On-Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =15A (note3)	-	0.25	0.33	Ω
Forward Transconductance	g _{fs}	V _{DS} =10V, I _D =15A (note3)	-	31	-	S
Dynamic Characteristics						
Input capacitance	C _{iss}	V _{DS} =25V, V _{GS} =0V, f=1.0MHz(note4)	-	4690	-	pF
Output capacitance	C _{oss}		-	421	-	pF
Reverse transfer capacitance	C _{rss}		-	15	-	pF
Switching-Characteristics						
Turn-On delay time	t _{d(on)}	V _{DS} =750V, I _D =4A, R _g =25Ω (note3,4)	-	76	-	ns
Turn-On rise time	t _r		-	52	-	ns
Turn-Off delay time	t _{d(Off)}		-	338	-	ns
Turn-Off rise time	t _f		-	76	-	ns
Total Gate Charge	Q _g	V _{DS} =750V, I _D =4A, V _{GS} =10V (note4)	-	96	-	nC
Gate-Source charge	Q _{gs}		-	26	-	nC
Gate-Drain charge	Q _{gd}		-	31	-	nC
Drain-Source Diode Characteristics and Maximum Ratings						
Maximum Continuous Drain-Source Diode Forward Current	V _{SD}	V _{GS} =0V, I _S =15A (note3)	-	-	1.2	V
Diode Forward Current	I _S	TC=25℃	-	-	30	A
Reverse recovery time	T _{rr}	I _S =4A, di/dt=100A/μs V _R =950V, V _{GS} =0V	-	0.4	-	us
Reverse Recovery Charge	Q _{rr}		-	3.9	-	uC

Thermal Characteristics

Parameter	Symbol	Unit	
Thermal Resistance, junction to Case	$R_{th(j-C)}$	0.43	°C/W
Case to Sink Thermal Resistance, junction-Ambient	$R_{th(C-A)}$	40	



Order Message

Marking	Package
MS30N95HGC0	TO-247


Notes:

1. Repetitive Rating : Pulse width limited by maximum junction temperature
2. $L = 15 \text{ mH}$, $I_{AS} = 10 \text{ A}$, $V_{DD} = 50 \text{ V}$, $R_G = 25 \text{ } \Omega$, Starting $T_J = 25^\circ\text{C}$
3. Pulse Test : Pulse width $\leq 300 \mu\text{s}$, Duty cycle $\leq 2\%$
4. Essentially independent of operating temperature


Electrical Characteristics




On-Region Characteristic@125°C




Transfer Characteristics




Transconductance




On-Resistance Variation vs Drain Current and Gate Voltage








On-Resistance Variation vs Temperature



Body Diode Forward Voltage Variation with Source Current and Temperature





Package Mechanical DATA

