




NOTES:

1. MATERIAL:

- 1.1. HOUSING: LCP,COLOR IS GRAY,HIGH TEMPERATURE PLASTIC;
- 1.2. CONTACT: BRASS(H65 T=0.20mm);
- 1.3. SHELL: COLD ROLLED IRON(SPCC,T=0.50mm);

2. FINISH:

2.1. TERMINAL:

CONTACT AREA: GOLD PLATED G/Fu"(2.0 AREA) ;
SOLDER AREA: PLATED OVER TIN;

2.2. SHELL: NI PLATED OVER ALL ;

4. ELECTRICAL:

4.1. VOLTAGE RATING: 40 VAC RMS;

4.2. CURRENT RATING: 0.5 AMP;

4.3. CONTACT RESISTANCE: 30mΩ MAX.;

4.4. WITHSTAND VOLTAGE: 500 VAC RMS

50(60)Hz,1MIN.;

4.5. INSULATION RESISTANCE: 100MEGOHMS MIN @500V DC;

5. MECHANICAL:

5.1. MATING FORCE: 44.1N MAX.;


5.2. UNMATING FORCE: 9.8N MIN;

5.3. OPERATING LIFE: 10000 CYCLES MIN.;

6. ENVIRONMENTAL:

6.1. STORAGE TEMPERATURE RANGE:-40°C~+85°C;

6.2. OPERATION TEMPERATURE RANGE:-25°C~+70°C;



			GENERAL TOLERANCE		制图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK				
			X.X	±0.30	批准 APPROVAL	产品名称 TITLE	HDMI 铁无点镍2.0	版本 REV.	A
1	初版发行		X.XX	±0.20	比例 SCALE	产品料号 PART NO.	HDMI-01	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/3
			Angle	±3.0°					