






Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000M Ω Min
Contact Resistance:20m Ω Max
Operation Temperature:-40° to+105°
Insulator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240° C for30-60seconds
(260° C for5seconds)

P/N	PIN	$DIM. A$	$DIM. B$
$HMT-PM1.0-2-2PL$	$2*2$	1.00	2.00
$HMT-PM1.0-2-3PL$	$2*3$	2.00	3.00
$HMT-PM1.0-2-4PL$	$2*4$	3.00	4.00
$HMT-PM1.0-2-5PL$	$2*5$	4.00	5.00
$HMT-PM1.0-2-6PL$	$2*6$	5.00	6.00
$HMT-PM1.0-2-7PL$	$2*7$	6.00	7.00
$HMT-PM1.0-2-8PL$	$2*8$	7.00	8.00
$HMT-PM1.0-2-9PL$	$2*9$	8.00	9.00
.....			
$HMT-PM1.0-2-40PL$	$2*40$	$(PIN-1)$	(PIN)



RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
X.° ±0.30	X.° ±5°	PART NO.	TITLE:		
X.X° ±0.20	X.X° ±1°	HMT-PM1.0-2-NPL	1.0FH H2.0 2xNPin SMT W2.5 型 PC3.8 PB2.3 6T		
X.XX°±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET