







Current Rating:1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000M Ω Min
Contact Resistance:20m Ω Max
Operation Temperature:-40° to+105°
Insulator Material:Polyester(UL94V-0)
Contact Material:Brass
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp: 240° C for30-60seconds
(260° C for5seconds)




P/N	PIN	$DIM. A$	$DIM. B$
$HMT-PZ2.54-2-2PL$	$2*2$	1.27	2.54
$HMT-PZ2.54-2-3PL$	$2*3$	2.54	3.81
$HMT-PZ2.54-2-4PL$	$2*4$	3.81	5.08
$HMT-PZ2.54-2-5PL$	$2*5$	5.08	6.35
$HMT-PZ2.54-2-6PL$	$2*6$	6.35	7.62
$HMT-PZ2.54-2-7PL$	$2*7$	7.62	8.89
$HMT-PZ2.54-2-8PL$	$2*8$	8.89	10.16
$HMT-PZ2.54-2-9PL$	$2*9$	10.16	11.43
.....			
$HMT-PZ2.54-2-50PL$	$2*50$	$(PIN-1)_{x1.27}$	$(PIN)_{x1.27}$



RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN <i>Shenzhen Huamingtong Electronics Co., Ltd</i>			
X.° ±0.30	X.° ±5°	PART NO.	TITLE:		
X.X° ±0.25	X.X° ±1°	HMT-PZ2.54-2-NPL	1.27PH H1.0 2xnPin SMT W3.4 PC5.5 PA4.0 PB1.5 L7.2 6T		
X.XX°±0.20	X.XX°±0.5°	DESIGN: <i>James</i>	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: <i>Talen</i>		A4	MM
		APPD: <i>Sophia</i>		SCALE	SHEET
					N:A