






电气性能

NOTES:

1. MATERIAL:
 - 1.1. HOUSING: PA9T, COLOR IS BLACK;
 - 1.2. CONTACT: PHOSPHOR COPPER (C5191, T=0.25mm);
2. ELECTRICAL:
 - 2.1. VOLTAGE RATING: 30 VAC RMS;
 - 2.2. CURRENT RATING: 0.5 AMP;
 - 2.3. CONTACT RESISTANCE: 30MILLIOHMS MAX.;
 - 2.4. WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz, 1MIN.;
 - 2.5. INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
3. MECHANICAL:
 - 3.1. MATING FORCE: 5~25N;
 - 3.2. UNMATING FORCE: 5~25N;
 - 3.3. OPERATING LIFE: 5000 CYCLES;
4. PLATING:
 - 4.1. TERMINAL:
NI PLATING OVER ALL,
TIN PLATING ON SOLDER AREA,
5. ENVIRONMENTAL:
 - 5.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
 - 5.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;
6. SALT SPRAY TEST: 8H (EXCLUDING RIVETED BENDS)

序号	品名	材质	电镀/颜色	备注
A	基座	PA9T	黑色	
B	端子	C5191	焊区镀锡 全周镀镍	

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	DRAWING				
			审 核		CHECK				
			X. X	±0.30	批 准	产品名称	313耳机3节贴片 黑色	版 本	A
			X. XX	±0.20	APPROVAL	TITLE		REV.	
			X. XXX	±0.10	比 例	产品料号	HC-PJ-3133-6P-S	单 位	mm
			SCALE			PART NO.		UNITS	
			Angle	±3.0°	投 影	材 料		页 次	1/1
			MODIFY DATE		Projection	MATERIAL		SHEET	