





- NOTES:
- MATERIAL:
 - HOUSING: PPA, COLOR IS BLACK;
 - CONTACT: PHOSPHOR COPPER (C5191, T=0.2mm);
 - FINISH:
 - TERMINAL:
CONTACT AREA: NI PLATED OVER ALL;
SOLDER AREA: SN PLATED OVER ALL;
 - ELECTRICAL:
 - VOLTAGE RATING: 30 VAC RMS;
 - CURRENT RATING: 0.5 AMP;
 - CONTACT RESISTANCE: 30MILLIOHMS MAX.;
 - WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz, 1MIN.;
 - INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
 - MECHANICAL:
 - MATING FORCE: 5~25N;
 - UNMATING FORCE: 5~25N;
 - OPERATING LIFE: 5000 CYCLES;
 - ENVIRONMENTAL:
 - STORAGE TEMPERATURE RANGE: -40°C~+85°C;
 - OPERATION TEMPERATURE RANGE: -25°C~+70°C;
 - SALT SPRAY TEST: 8H (EXCLUDING RIVETED BENDS)



序号	品名	材质	电镀/颜色	备注
A	基座	PPA	黑色	
B	端子	C5191	镀镍 镀锡	

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核				
			X. X	±0.30	批 准	产品名称	320D 红铜插件 黑色	版本	A
			X. XX	±0.20	APPROVAL	TITLE		REV.	
			X. XXX	±0.10	SCALE	产品料号	HC-PJ-320D-4P-S	单位	mm
			Angle	±3.0°	投影	PART NO.		UNITS	
序号	变更内容	日期			Projection	材料		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE				MATERIAL		SHEET	