








NOTES:

- MATERIAL:
 - HOUSING: PPA, COLOR IS BLACK;
 - CONTACT: PHOSPHOR COPPER ;
- FINISH:
 - TERMINAL:
CONTACT AREA: NI PLATED OVER ALL;
SOLDER AREA: SN PLATED OVER ALL;
- ELECTRICAL:
 - VOLTAGE RATING: 30 VAC RMS;
 - CURRENT RATING: 0.5 AMP;
 - CONTACT RESISTANCE: 30MILLIOHMS MAX.;
 - WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz,1MIN.;
 - INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
- MECHANICAL:
 - MATING FORCE: 5~25N;
 - UNMATING FORCE: 5~25N;
 - OPERATING LIFE: 5000 CYCLES;
- ENVIRONMENTAL:
 - STORAGE TEMPERATURE RANGE: -40°C~+85°C;
 - OPERATION TEMPERATURE RANGE: -25°C~+70°C;
- SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)

电气性能

序号	品名	材质	电镀/颜色	备注
A	基座	PPA	黑色	
B	端子	磷铜0.25T	镀银	



			GENERAL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	±0.30	批 准 APPROVAL	产品名称 TITLE	320D 3.5耳机插座 贴片	版 本 REV.	A
			X. XX	±0.20	比 例 SCALE	产品料号 PART NO.	HC-PJ-320D-3P-S	单 位 UNITS	mm
			X. XXX	±0.10					
1	初版发行				投 影 Projection		材 料 MATERIAL	页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	±3.0°					