

This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	19/03/17	19/03/17

1 Electrical



1.1 Impedence	50 Ω
1.2 Frequency	DC~6GHz
1.3 Dielectric withstanding voltage	1000V(volts RMS)
1.4 Center contact resistance	$\leq 3\text{M}\Omega$
1.5 Outer contact resistance	$\leq 2\text{M}\Omega$
1.6 Insulation resistance:	$\geq 5000\text{M}\Omega$

2 Environmental&Mechanical

2.1 Temperature range	-40℃~+85℃
2.2 RoHs Compliant	
2.3 Durability	>500 cycles


3 Materials&plating

3.1 Body:	Brass; gold plated
3.2 Insulator:	Teflon
3.3 Contact Pin:	Brass, gold plated
3.4 Nut:	Brass, gold Plated
3.5 Gasket:	Silicon Rubber (red color)



Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 19/03/17	TITLE: RF Connector SMA Male PCB Mount	 成都恒利泰科技有限公司 Chengdu HenryTech Technology co., Ltd			
ENGINEER: L.yu 19/03/17					
APPROVED: W.yi 19/03/17					
TOLERANCES UNLESS OTHERWISE SPECIFIED X ±0.50 .X ±0.20 .XX ±0.10 ANGLES ±1°		 DIMENSION IN MILLIMETERS (mm)			
PART NO: HL-SMA-JHDC3		SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A