









<i>PIN number variable size comparison table</i>				
<i>PART NO</i>	<i>PIN</i>	<i>A</i>	<i>B</i>	<i>C</i>
<i>HMT-HA2. 54-WT2P</i>	<i>2</i>	<i>2. 50</i>	<i>10. 00</i>	<i>8. 30</i>
<i>HMT-HA2. 54-WT3P</i>	<i>3</i>	<i>5. 00</i>	<i>12. 50</i>	<i>10. 80</i>
<i>HMT-HA2. 54-WT4P</i>	<i>4</i>	<i>7. 50</i>	<i>15. 00</i>	<i>13. 30</i>
<i>HMT-HA2. 54-WT5P</i>	<i>5</i>	<i>10. 00</i>	<i>17. 50</i>	<i>15. 80</i>
<i>HMT-HA2. 54-WT6P</i>	<i>6</i>	<i>12. 50</i>	<i>20. 00</i>	<i>18. 30</i>
<i>HMT-HA2. 54-WT7P</i>	<i>7</i>	<i>15. 00</i>	<i>22. 50</i>	<i>20. 80</i>
<i>.....</i>	<i>.....</i>	<i>.....</i>	<i>.....</i>	<i>.....</i>
<i>HMT-HA2. 54-WT16P</i>	<i>16</i>	<i>37. 50</i>	<i>45. 00</i>	<i>43. 30</i>



1. *BASE: LCP*
2. *PIN: Brass*
3. *Solder Tab: Brass*

1. Spacing: 2.5
2. Voltage Rating: 250V AC DC
3. Current Rating: 3A AC DC
4. Insulation Resistance: $800M\Omega$ Min
5. Contact Resistance: $20m\Omega$ Max
6. Withstanding voltage: 1000V AC 1/Minute
7. Temperatuer Range: $-25^{\circ}C \sim + 85^{\circ}C$



GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO.		TITLE:	
.XX ±0.20	X.X° ±1°	HMT-HA2.54-WTNP		WAFER XHB2.54 卧贴带扣	
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1