

Technical drawing of a mechanical part, showing four views: front, top, side, and bottom. The drawing includes various dimensions and tolerances.

Front View (Top Left): Shows the front profile of the part. Dimensions include a width of 6.80 ± 0.00 to $+0.20$ and a height of 0.5 .

Top View (Bottom Left): Shows the top profile of the part. Dimensions include a width of 16.30 ± 0.25 and a height of 0.35 ± 0.20 . A hole is indicated with a diameter of $\phi 1.1$.

Side View (Top Right): Shows the side profile of the part. Dimensions include a width of 13.10 ± 0.10 and a height of 14.6 . A hole is indicated with a diameter of $\phi 1.1$. Other dimensions include 4.50 ± 0.25 , 2.0 , and 7.0 .

Bottom View (Bottom Right): Shows the bottom profile of the part. Dimensions include a width of 18.80 and a height of 2.4 . A hole is indicated with a diameter of $\phi 1.200$. Other dimensions include 2.7 , 7.0 , 2.0 , 3.0 , 2.5 , 15.3 , and 2.0 .