DCE0510D2

1-Line Bi-directional TVS Diode

Features

- Ultra small package: 1.0 x 0.6 x 0.5mm
- Protects one data or power line
- Ultra low leakage: nA level
- Operating voltage: 5V
- Low clamping voltage
- 2-pin leadless package
- Complies with IEC 61000-4-2 (ESD): Air ±30kV, Contact ±30kV
- IEC 61000-4-5 (Lightning): 8A (8/20μs)
- RoHS Compliant

DFN1006-2L



Mechanical Data

- Package: DFN1006-2 (1.0 x 0.6 x 0.5mm)
- Case Material: "Green" Molding Compound
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminal Connections: See Diagram Below

Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants (PDAs)
- Notebooks, Handhelds and Portable Instrumentation
- Digital Cameras and Audio Players
- Peripherals
- Keypads, Side Keys, LCD Displays

Ordering information

Order code	Marking	Package	Packaging option	Base quantity	Packaging specification
DCE0510D2	PB	DFN1006-2L	Tape and reel	10000pcs / reel	EIA STD RS-481

Absolute Maximum Ratings

Ratings at 25 °C, ambient temperature unless otherwise specified

Parameter	Symbol	Value	Unit
Peak Pulse Power (T_P=8/20μs)	P_{PP}	100	W
ESD contact/air discharge (IEC-61000-4-2)	V_{ESD}	±30/±30	kV
Peak Pulse Current (T_P = 8/20μs)	I_{PP}	8	A
Junction Temperature	T_J	-55 to +125	℃
Operation temperature	T_{OP}	-55 to +125	℃
Storage temperature	T_{STG}	-55 to +150	℃

DongChen@TVS

Electrical Characteristics

(T_A = 25 °C unless otherwise specified)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Reverse stand-off Voltage	V_{RWM}		-	-	5	V
Holding Voltage	V_{BR}	IT = 1mA	6	-	8	V
Reverse Leakage Current	I_R	VRWM = 5V	-	-	0.2	uA
Clamping Voltage	V_C	IPP = 1A,t_p=8/20μs	-	-	8	V
Clamping Voltage	V_C	IPP = 8A,t_p=8/20μs	-	-	12.5	V
Junction Capacitance	C_J	V_R=0V, f=1MHz	-	15	-	pF

DongChen@TVS

Typical Performance Characteristics (T_A=25℃ unless otherwise Specified)



Junction Capacitance vs. Reverse Voltage



Peak Pulse Power vs. Pulse Time



Clamping Voltage vs. Peak Pulse Current (tp = 8/20μs)



Power Derating Curve



8 X 20μs Pulse Waveform



ESD Clamping Voltage

8 kV Contact per IEC61000−4−2

DongChen@TVS

Package Dimensions



Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	0.95	1.00	1.05
E	0.55	0.60	0.65
b	0.45	0.50	0.55
L	0.20	0.25	0.30
e		0.65 BSC	
A	0.40	0.50	0.55
A1	0	0.02	0.05
c	0.12	0.15	0.18
h	0.07	0.12	0.17
L1		0.05 REF	

Pad Dimensions



Unit:mm

Package Information



DongChen@TVS

Important Notice

DongChen Electronics reserves the right to make changes without further notice to any products herein.

DongChen Electronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does DongChen Electronics assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

“Typical” parameters which may be provided in DongChen Electronics data sheets and/or specifications can and do vary in different applications and actual performance may vary over time.

All operating parameters, including “Typicals,” must be validated for each customer application by the customer’s technical experts.

DongChen Electronics does not convey any license under its patent rights nor the rights of others.

The products listed in this document are designed to be used with ordinary electronic equipment or devices.

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, aerospace machinery, nuclear-reactor controllers, fuel controllers, and other safety devices), please be sure to consult with our sales representative in advance.

DongChen@TVS

Head Office
Contact Information:
DongChen Electronics Co.,Ltd.
Address：2F., No.407, Sec. 2, Longgang Rd.,Zhongli Dist., Taoyuan City 32097, Taiwan (R.O.C.)
Tel: 03-284-1808
Fax: 03-284-1404
Mail:dc@dongchen.com.tw
Web:www.dongchen.com.tw