

















Bemerkungen








- 1 ALL RADII R0.3 EXCEPT AS NOTED
Nicht benoetigte Radien R0.3
- 2 TE-PART NO.:
TE-Teile Nr.:
- 3 TE-ASSY-NO.: SEE TABLE
TE-Assy Nr.: siehe Tabelle
- 4 PRODUCTION-DATE WITH DATE INSERT, Ø3
Produktionsdatum mit Datumstempel, Ø3
- 5 AREA FOR CAVITY MARKING
Platz fuer Nestmarkierung
- 6 REVISION ACCORDING TO PLASTIC PART-REV.
Aenderungsindex gemaeß Kunststoffteil-Rev.
- 7 PULL-OUT FORCE PER PIN > 25 N
Auszugskraft pro Steckerstift > 25 N
- 8 DIMENSION MEASURED AT ANGLE SOURCE
Maße am Grund gemessen
- 9 LETTER INSERTS ON CHOICE OF MANUFACTOR
Schriften nach Wahl des Herstellers
- 10 CAVITY IDENTIFICATION
Kammerbezeichnung
- 11 MATERIAL IDENTIFICATION
Materialkennzeichen
- 12 TE-LOGO
TE-Logo
- 13 SPECIFICATION OF PIN SEE 208-15584-1
Ausfuehrungsvorschrift Stift 208-15584-1
- 14 :
- 15 PACKAGING SEE SPEC V1563144
Verpackung siehe Spez.V1563144

1563144-1 Kodierung "schwarz" wie dargestellt
1563144-1 COIDNG "BLACK" AS SHOWN


1-1563144-2	TAPE&REEL 	A	WHITE/weiß	CONTACT	Cu Sn 6	VORVERZINNT	3	2	TE PN: 953697-2
				MQS PIN HOUSING	PPA-GF25	WHITE/weiß	1	1	
1-1563144-1	TAPE&REEL 	B 	BLACK/schwarz	CONTACT	Cu Sn 6	VORVERZINNT	3	2	TE PN: 953697-1
				MQS PIN HOUSING	PPA-GF25	BLACK/schwarz	1	1	
1563144-1	LOOSE PIECE	B	BLACK/schwarz	CONTACT	Cu Sn 6	VORVERZINNT	3	2	TE PN: 953697-1
				MQS PIN HOUSING	PPA-GF25	BLACK/schwarz	1	1	
TE ASSY NO	PACKAGING	REV.	CODING KODIERUNG	DESCRIPTION BENENNUNG	MATERIAL	COLOR / SURFACE	PCS.	POS	SUITABLE SOCKET HOUSING PASSENDES BUCHSENGEHÄUSE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG V. Holzmann	23JUL2007	ASSEMBLY COUNTERMOUNT	
		CNR	23JUL2007	STE TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD -		PINHEADER MQS 3 POS 90 DEG.	
		PRODUCT SPEC		Stiftwanne MQS 3 pol. 90 Gr.	
		-		-	
		APPLICATION SPEC		-	
		-		SIZE	
		ANGLES		CASE CODE	
MATERIAL	FINISH	WEIGHT	DRAWING NO	RESTRICTED TO	
siehe Tabelle	-	-	A1 00779	C=1563144	
-	-	-	CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 2 REV B3

REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN
-	-	SEE SHEET 1	-	-



1-1563144-1
AS SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN V. Holzmann	23JUL2007	 TE Connectivity								
		CHE	23JUL2007									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	PINHEADER MQS 3 POS 90 DEG.							
		0 PLC ±		PRODUCT SPEC	Stiftwanne MQS 3 pol. 90 Gr.							
1 PLC ±		-	-									
2 PLC ±		APPLICATION SPEC	-									
3 PLC ±		WEIGHT	-									
4 PLC ±		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO						
ANGLES ±°		A1		00779	C=1563144							
FINISH		CUSTOMER DRAWING		SCALE	5:1	SHEET	2	OF	2	REV	B3	
MATERIAL siehe Tabelle												
-												