










- NOTES:
1. MATERIAL:
 - 1.1. HOUSING: LCP ,COLOR IS GRAY;
 - 1.2. CONTACT: PHOSPHOR COPPER (C5191 T=0.30mm) ;
 - 1.3. SHELL: BRASS (H65 T=0.2mm);
 2. FINISH:
 - 2.1. CONTACT: PLATED OVER NI,GOLD PLATED G/Fu";
 - 2.2. SHELL: PLATED OVER NI;
 4. ELECTRICAL:
 - 4.1. VOLTAGE RATING: 125 VAC RMS;
 - 4.2. CURRENT RATING: 1.5 AMP;
 - 4.3. CONTACT RESISTANCE: 35MILLIOHMS MAX.;
 - 4.4. WITHSTAND VOLTAGE: 500 VAC RMS 50(60)Hz,1MIN.;
 - 4.5. INSULATION RESISTANCE: 500MEGOHMS MIN @500V DC.;
 5. MECHANICAL:
 - 5.1. MATING/UNMATING FORCE: 22N MAX.;
 - 5.2. RETENTION STRENGTH: 50N MIN.;
 - 5.3. OPERATING LIFE: 750 CYCLES MIN.;
 6. ENVIRONMENTAL:
 - 6.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
 - 6.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;



			GENERL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	± 0.30	批 准 APPROVAL	产 品 名 称 TITLE	网 络 插 座 RJ沉板 (全包铜壳编带)	版 本 REV.	A
1	初版发行		X. XX	± 0.20	比 例 SCALE	产 品 料 号 PART NO.	HC-RJ45-055-4	单 位 UNITS	mm
			X. XXX	± 0.10		材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变 更 内 容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	± 3. 0°	投 影 Projection				