







ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE



Main technical performance	
Rated electrical load	DC 30V 3A
Contact resistance	≤0.03 Ω
Insulation resistance	≥100MΩ
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-20℃~+70℃
service life	5000cycles



PCB.WELDING DRAWING

COSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECK			
APPROVAL			
TOLERANCES ARE		TITLE	DC电源连接器C2.0带螺母（直插）
30-150	±0.35	PART NO.	LAIL-DC30-D5.6C2.0-L
10-30	±0.2		
5-10	±0.15		
0-5	±0.1		
ANGLE		DWG.NO.	
±3°		Units mm	
		Projection	