

承 认 书

SPECIFICATION FOR APPROVAL

客 户 名 称

CUST OMER:

客 户 料 号

CUS PART NO:

品 名 规 格

PART NAME :

SH-BH3.5-2AWT

料号

FAC PART NO:

A35001

客户:

签章:

日期: 年 月 日

采购部	工程部	批 准


深海 :

日期: 2020 年 12 月 29 日

工程部	销售部	批 准

备注: 承认签章后请回复一份(或复印件)给我司, 其余由贵司留作存档。如果在签章的承认书(或复印件)回复给我司之前, 下了有关此规格产品的订单且又无特别说明, 那么我司就确定贵司已完全承认了。

Please return one specification or one copy of it with your chop and signature of approval and retain the others for your record. In the event of an order being placed for this part number before the chop and signed with specification (or copy) is returned and without special explanation , it will be assumed that full approval have been given.



1、SCOPE

适用范围

The contents of specifications for BH3.5 series connector strip, including product performance, test methods and inspection requirements

本规格书内容适用于 BH3.5 系列条形连接器，包含了产品的性能、试验方法和检验要求

2、APPLICABLE STANDARDS

适用的标准

- | | | |
|-----|----------|---|
| 2.1 | GB/T2421 | Testing method for Environmental of Electrical Connectors Class 1 :
General Principles |
| | GB/T2421 | 电工电子产品环境试验 第一部分 总则 |
| 2.2 | GB/T2423 | Testing method for Environmental of Electrical Connectors |
| | GB/T2423 | 电工电子产品环境试验方法 |
| 2.3 | GB/T2424 | Testing method for Environmental of Electrical Connectors |
| | GB/T2424 | 电工电子产品环境试验导则 |
| 2.4 | GB/T5095 | Testing Procedure/method for components of electric equipment
电子设备用机电元件基本试验规程及测量方法 |

3、USE CONDITION

使用条件

- 3.1 Ambient temperature Range:-25℃~+105℃**
环境温度：-25℃~+105℃
- 3.2 Applicable Wire Sizes:AWG#24~#28**
适用线规：AWG#24~#28
- 3.3 Applicable PC board thickness:0.8~1.6mm**
适用 PC 板厚度：0.8~1.6mm

4、Appearance and Dimension

外观及尺寸

- 4.1 Appearance:Product surface without defect、dirt、crack、and mechanical damang, Contact without rust,plating not oxidized and not peeled.**
产品表面不应有对制品有害的缺陷、污垢、裂痕及机械损伤；接触件无锈蚀、镀层氧化、脱落等现象.
- 4.2 Dimension:According to drawings**
外形尺寸：依照附图
- 4.3 Exchangable:Exchangable with same specification products.**
互换性：相同规格应能互换

浙江深海电子有限公司

5、Material

材 料

P/N 零件名称	Type 类 型	Material 材 料	Finish 表面处理	Explain 说 明
Terminal 端子-PT	Contact 插 簧	Phosphor bronze 锡青磷铜 厚 0.20mm	Tin Plating100u".MIN 镀锡100u".MIN	RoHS
Terminal 端子-RT	Contact 插 簧	Phosphor bronze 锡青磷铜 厚 0.20mm	Tin Plating100u".MIN 镀锡100u".MIN	
Housing 孔座-P	Plastic 塑 壳	Nylon66 UL94V-0	Color: White 颜色：白色	
Housing 孔座-R	Plastic 塑 壳	Nylon66 UL94V-0	Color: White 颜色：白色	
Wafer 弯针座	Plastic 塑 壳	Nylon6T UL94V-0	Color: Beige 颜色：米色	
	Contact 插 针	Brass 黄铜 厚 0.50mm	Tin Plating100u".MIN 镀锡100u".MIN	
	Solder foot 焊 脚	Phosphor bronze 锡青磷铜 厚 0.25mm	Tin Plating100u".MIN 镀锡100u".MIN	
Wafer 卧贴针座	Plastic 塑 壳	LCP UL94V-0	Color: Beige 颜色：米色	
	Contact 插 针	Brass 黄铜 厚 0.50mm	Tin Plating100u".MIN 镀锡100u".MIN	
	Solder tab 焊护耳	Phosphor bronze 锡青磷铜 厚 0.20mm	Tin Plating100u".MIN 镀锡100u".MIN	

6、Electrical Performance

电 气 性 能

N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
6.1	Current Rated 额定电流		1A AC DC
6.2	Voltage Rated 额定电压		1400V AC DC
6.3	ContactResistance 接触电阻	A maximum voltage of 20mV and a maximum current of 100mA are applied to the Mate connector 组合状态下的连接器，两端施以最大测试电压 20 mV 以及最大测试电流 100 mA Does not include wire resistance 不包含电线阻抗	Initial value Less than 20m Ω 初始值≤20 m Ω

浙江深海电子有限公司

N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
6.4	withstandvoltage 耐电压	Apply 3800V AC(rms)for 1 minute and the leakage current shall not exceed 0.5mA to the adjacent terminal and ground of the Mate connectors 组合状态下的连接器，相邻两导体末端各施以电压 3800V AC(有效值)时间 1 分钟，且漏电流必须小于 0.5mA(毫安培)	No breakdownor flashover 无击穿或者产生火花
6.5	InsulationResistance 绝缘电阻	Apply 500V DC(rms)for 1 minute between adjacent contacts to measure the insulation resistance 相邻两接触导体，1 分钟时间内施予 500V DC 电压，测量期间的绝缘阻抗值	More than 1000 M Ω $\geq 1000M \Omega$

7、Mechanical Performance:

机 械 性 能

N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
7.1	Terminal crimping wire strength 端子压接导线强度	Terminal crimping wires, axial per minute to 25 $\pm$ 3mm rate of the pullout force 端子所压接电线，以每分钟 25 $\pm$ 3mm 速率之轴向拔出力	AWG#24 wire AWG#24 导线 More than 30N $\geq 30N$
			AWG#26 wire AWG#26 导线 More than 20N $\geq 20N$
			AWG#28 wire AWG#28 导线 More than 13N $\geq 13N$
7.2	Fixed terminals and hole seat 端子与孔座固定力	The terminal and the hole seat, at a rate per minute to 25 $\pm$ 3mm along the wire direction are pulled out from the hole in the seat capacity 端子与孔座配合，以每分钟 25 $\pm$ 3mm 的速率沿导线方向将端子从孔座中拔出的力	Per contact 单一接触点 More than 15N $\geq 15N$
7.3	Singlecontact insertion force 单接触插入力	The Housing together with the terminal ends with Wafer matched, at a rate per minute to 25 $\pm$ 3mm, inserting force test 孔座连同端子与针座两端互配，以每分钟 25 $\pm$ 3mm 的速率，作插入力测试	Less than 5N $\leq 5N$
7.4	Single contact withdrawal force 单接触拔出力	The Housing together with the terminal ends with Wafer matched, at a rate per minute to 25 $\pm$ 3mm, as the pull-out test 孔座连同端子与针座两端互配，以每分钟 25 $\pm$ 3mm 的速率，作拔出力测试	More than 0.5N $\geq 0.5N$
7.5	Pin Retention force PIN 针固定力	Exerts a force on the pin end, at a rate per minute 25 $\pm$ 3mm, until the needle exit seat pull-out force 在针脚前端施加力，以每分钟 25 $\pm$ 3mm 的速率，直到针退出针座的拔出力	Per contact 单一接触点 More than 10N $\geq 10N$

浙江深海电子有限公司

N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
7.6	Durability 耐久性	Mate connectors up 30 cycles at a Maximun rate of 10cycles per minute prior toenvironmental test 组合状态下的连接器且未经环境测试，每分钟内进行 10 次嵌入与拔出，连续 30 次嵌入与拔出往返测试	Contact Resistance $\leq 20 \text{ m}\Omega$ 接触电阻 $\leq 20 \text{ m}\Omega$
7.7	Vibration 振动	Connector combination state of the welding circuit board as test samples, the request in accordance with the following specifications, resistance to vibration test, whether to produce discontinuous current determined during the experiment (off) phenomenon, after the experiment measuring contact resistance 组合状态下的连接器焊接电路板上作为试验样品，依照如下规格要求，进行耐振动试验，试验过程中确定是否产生不连续电流（断电）现象，试验过后测量接触电阻值 Frequency(频率):10-55-10 Hz/minute Amplitude(振幅):1.5mm p-p Direction(方向): 1、Axis of up and down 上下轴向(Y 轴) 2、Axis of right the left 左右轴向(X 轴) 3、Axis of front and back 前后轴向(Z 轴) Period(周期):2 hous for each direction 每一个轴向持续 2 小时	Appearance: No damage 外观：无损伤 Contact Resistance $\leq 20 \text{ m}\Omega$ 接触电阻 $\leq 20 \text{ m}\Omega$ current Discontinuity: 1 micro second Max 电流中断：1 μ sec Max

8、Endurance Characteristics:

环 境 性 能

N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
8.1	Thermal Aging 高温老化试验	Connector combination condition is placed in the oven, the request in accordance with the following specifications, high temperature aging test, after the test and measurement of contact resistance 组合状态下的连接器放置于加热烤箱中，依照如下规格要求，进行高温老化试验，试验后并测量接触电阻值 Temperature:85 $\pm$ 2 $^{\circ}\text{C}$ Period:96 hours continuously 温度：85 $\pm$ 2 $^{\circ}\text{C}$ 周期：持续 96 小时	Appearance: No damage 外观：无损伤 Contact Resistance $\leq 20 \text{ m}\Omega$ 接触电阻 $\leq 20 \text{ m}\Omega$

浙江深海电子有限公司

N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
8.2	Temperature 温升	Mate connector measure the temperature rise of contact when the maximum rated current is passed 组合状态下的连接器，通过最大容许电流测量导体温度上升值	30℃ Max
8.3	Humidity 恒定潮湿	Connector combination under the condition of constant temperature and humidity place space, in accordance with the requirements of the following specifications, constant temperature and humidity test, after the experiment measuring contact resistance, insulation resistance and withstand voltage test 组合状态下的连接器放置恒定温度的湿气空间，依照如下规格要求，进行恒温恒湿试验，试验过后测量接触电阻、绝缘电阻以及耐电压测试 Temperature: 40 ± 2 °C Relative humidity:90-95%RH Period:96 hours continuously 温度:40±2℃ 相对湿度:90-95% 周期：持续 96 小时	Appearance: No damage 外观：无损伤 Contact Resistance: ≤20m Ω 接触电阻：≤20 m Ω Insulation Resistance: ≥ 1000M Ω 绝缘电阻：≥1000M Ω No breakdown or flashover 无击穿或者产生火花
8.4	Temperature cycling 温度循环	The combined state of connectors as test samples, in accordance with the requirements of the following specifications, thermal shock test, after the test measuring contact resistance, insulation resistance, and resistance to voltage 组合状态下的连接器作为试验样品，依照如下规格要求，进行冷热冲击试验，试验后测量接触电阻、绝缘电阻、以及耐电压测试 One cycle consists of: -55 ± 3℃,30min,Room temp.10-15 min 85 ± 3℃,30min,Room temp.10-15 min Total cycle: 5 cycle -55 ± 3℃,30 分钟，放置转换时间 10-15 分钟 85 ± 3℃,30 分钟，放置转换时间 10-15 分钟 循环次数：5 次	Same as paragraph 8.3 同 8.3 章节

浙江深海电子有限公司

N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
8.5	Salt spray 盐雾	The combined state of connector as test samples, salt spray test according to the following specifications, test samples will be clean again with the water to dry naturally, measurement of contact resistance 组合状态下的连接器作为试验样品，依照如下规格要求进行盐水喷雾试验，试验后将样品用清水冲干净自然凉干，测量接触电阻值 Temperature: 35±3℃ Solution: 5±1% Period: Stamping after tin plated for 8 hours Stamping before tin plated for 48 hours 温度：35±3℃ 浓度：5±1% 周期： 先电镀后冲压 8 小时 先冲压后电镀 48 小时	Appearance: No damage 外观：无损伤 Contact Resistance: ≤20m Ω 接触电阻：≤20 m Ω
8.6	Solder ability 可焊性	In accordance with the following specifications were placed tin soldering test 放置锡炉中依照如下规格进行焊锡试验 Solder Temperature:245±5℃ Immersion period:3±0.5S 焊锡温度：245±5℃ 沉浸周期：3±0.5S	Area of Soldering: ≥90% 焊锡面积：≥90%

浙江深海电子有限公司


N0. 序号	Ltem 项 目	Test mode 试验方法	Requirement 技术要求
8.7	Resistance to soldering heat 耐焊接热	anual soldering tin process Soldering time: 3±0.5S Soldering pot: 305±5℃ 手工烙铁焊锡工艺 焊接时间: 3±0.5S 焊接温度: 305±5℃ Mode of operation: 操作方式: Position DIP type needle solder, conductor or a fixed piece at the end of the 1.5mm distance DIP 型针座焊锡位置, 距离导体或固定片末端 1.5mm Position SMT type needle solder, conductor or a fixed piece at the end of the 0.5mm distance SMT 型针座焊锡位置, 距离导体或固定片末端 0.5mm Reflow soldering process Soldering time: 20 S Max Soldering pot: 255±5℃ 回流焊焊锡工艺 焊接时间: 20S 最大 焊接温度: 260±5℃ Please refer to the 9.1 solder reflow temperature curve 回流焊请参考 9.1 温度曲线图	Appearance: No damage 外观: 无损伤

9、The reflow temperature curve

回流焊温度曲线

9.1 SMT lead-free process temperature curve

SMT 无铅工艺温度曲线



10、Packaging Transportation Storage

包装、运输、贮存

10.1 Packaging

包装

- (1) **Terminal within the packaging for disc loading material packaging, plastic shell packaging for plastic bags, packaging bags, seat plates, tubes, mounted (paste) into the certificate, indicate the product name, specifications, quantity production date and other information**

端子内包装为盘装带料包装、胶壳内包装为塑料袋，针座包装为盘装、袋装、管装，装（贴）入合格证，注明产品名称、规格型号、数量生产日期等信息

- (2) **Exterior package is carton, facing the packing list, the packing list marked with product name, specification model, quantity, date of dispatch.**

外包装为纸箱，贴装箱单、装箱单上注明产品名称、规格型号、数量、出货日期

- (3) **The product in the box must not rock**

产品在箱内不晃动

10.2 Transportation

运输

Any vehicle can be adopted for the transportation, but moisture-proof and no mechanical damage, transport temperature to $-20^{\circ}\text{C} \sim +50^{\circ}\text{C}$

允许用任何方式运输，但需避免雨雪直淋和阳光照射，不能有碰撞和挤压等机械损伤，运输环境温度为 $-20^{\circ}\text{C} \sim +50^{\circ}\text{C}$

10.3 Storage

贮存

- (1) **The connector of packing finished should be in the ambient temperature between -10°C to $+40^{\circ}\text{C}$, Relative humidity $\leq 80\%$. To store in storehouse does not have acidic, alkaline air and other corrosive gas in the ambient air.**

包装完毕的连接器应在环境温度为 $-20^{\circ}\text{C} \sim +40^{\circ}\text{C}$ ，相对湿度 $\leq 80\%$ ，周围空气没有酸性，碱性及其它腐蚀性气体的库房中贮存

- (2) **Re-qualification test shall be conducted immediately while the storing duration exceed 6 months**

贮存期为 6 个月，超期 6 个月需从新检查