





TROQ Electronic Co.,Ltd.
CRYSTAL UNIT SPECIFICATIONS


Customer	
Production Name	SMD CRYSTAL SEAM 3.2*2.5
Customer P/N	N/A
TROQ P/N	RL270001605
Revision	A
Print Date	2026/6/15

Drawn	Checked	Approved
		



RoHS Compliant

Pb used in sealing glass material is exempt from EU directive




修订记录表

No.1666 Xianhua South Street Jinhua,Zhejiang,China TEL:86-579-89168688 FAX:86-579-89168699
<http://www.troq.com>


● ELECTRICAL PARAMETERS

谐振器产品技术指标	Min	TYP.	Max	Units
1、Holder Type(型号规格)	SEAM 3.2*2.5			
2、Mode of Oscillation (振动模式)	Fundamental			
3、Frequency (标称频率)	27.000000			MHz
4、Load Capacitance (CL) (负载电容)	9			pF
5、Shunt Capacitance (Co) (静态电容)	0		5	pF
6、Equivalent Resistance (谐振电阻)	30			Ω
7、Frequency Tolerance at 25℃ (调整频差)	-10	10		ppm
8、Stability over operation Temperature (温度频差)	± 20			ppm
9、Insulation Resistance (at DC 100V) (绝缘电阻)	500			MΩ
10、Drive Level (激励功率)		100		uw
11、Operating Temperature Range (工作温度范围)	-40	85		℃
12、Storage Temperature Range (储存温度范围)	-40	85		℃
13、Aging (老化率) First Year	± 3			ppm/year
Other(其他)	0			

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)



● Marking (标记)



● Load Capacitance (负载电容)

Load Capacitance (CL)	5.7	10	12	12.5	15	16	18
Code (代码)	A	B	C	D	E	F	G
Load Capacitance (CL)	20	22	27	30	32	∞	8
Code (代码)	H	J	K	M	N	S	R
Load Capacitance (CL)	7	9	13	7.5			Other
Code (代码)	T	V	W	X	Y	Z	P

● Table of Year and Month code 生产年月 (年份为12年一循环)

Month 月份	1	2	3	4	5	6	7	8	9	10	11	12
code 代码	A	B	C	D	E	F	G	H	K	M	N	P
Year 年份	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031
code 代码	a	b	c	d	e	f	g	h	k	m	n	p

	Week	First Week	Second Week	Third Week	Fourth Week	Fifth Week
Code	First Batch	1	2	3	4	5
	Second Batch	A	B	C	D	E
	Third Batch	F	G	H	J	K
	Fourth Batch	L	M	N	P	Q
	Fifth Batch	R	S	W	X	Y



illustrate: Nominal Frequency 25.000MHZ
说明: 标称频率 25.000MHZ

Load Capacitance 20pF
负载电容20pF


First week of January 2020 TROQ Production
2020年1月份第一周 TROQ 制造

● SUGGESTED REFLOW PROFILE (回流焊曲线图)


Total time:200sec.Max. (总时间: 200秒 最大)

Solder melting point:220℃ (熔点220 ℃)

Profiles Feature (特性)		Pb-Free Assembly
Average Ramp-up Rate(Ts max to Tp)	平均升温速度	3℃/second Max
Preheat	预热	
■ Temperature Min (Ts min)	最低温度	125℃
■ Temperature Max (Ts max)	最高温度	200℃
■ Time (ts min to ts max)	从最低到最高时间	(60~180) seconds
Time maintained above	维持上述时间	
■ Temperature(T1)	温度	217℃
■ Time(tp)	时间	(60~150) seconds
Peak/Classification Temperature(Tp)	最高点温度	260 ℃
Time within 5℃ of actual Peak Temperature(tp)	高温维持时间	(20~40) seconds
Ramp-down rate	降温速度	6℃/second max
Time 25℃ to Peak Temperature	从25℃到最高温度的时间	8 minutes max
Suggest reflow times	建议 reflow次数	3 Times max




● PACKING (包装) 3Kpcs/REEL



8.3. Reel dimension & Outline drawing

Material of the Reel : PS



● RELIABILITY SPECIFICATIONS (信赖度试验)

No	Test Item (测试项目)	Test Conditions (测试条件)	Reference (参考)
1	High Temperature High Humidity Storage (高温、高湿、储存)	Temperature: 85°C±3°C 温度: 85°C±3°C Relative Humidity: 85%RH 相对湿度: 85%RH Time: 96 Hours 时间: 96小时	JIS C5023
2	High Temperature Storage (高温储存)	Temperature: 125°C±3°C 温度: 125°C±3°C Time: 96 Hours 时间: 96小时	MIL-STD-883E Method 1005.8
3	Low Temperature Storage (低温储存)	Temperature: -40°C±3°C 温度: -40°C±3°C Time: 96 Hours 时间: 96小时	MIL-STD-883E Method 1013
4	Thermal Shock (温度冲击)	Temperature 1: -55°C±5°C 温度 1: -55°C±5°C Temperature 2: 85°C±5°C 温度 2: 85°C±5°C Temperature change between T1 and T2 5 min T1和T2温度在5分钟内改变 10 cycles maintain T1 and T2 for 30 minutes each one cycle 每次循环30分钟共10次	MIL-STD-202F Method 107 Condition A
5	RESISTANCE TO SOLDER HEAT (耐焊接热)	Solder Temperature: 260°C±5°C 焊槽温度: 260°C±5°C Time: 10±1 Seconds 时间: 10±1秒	MIL-STD-202F Method 210E
6	Solderability (可焊性)	The solder pot temperature is 245±5°C, dwell time 5±0.5sec 245±5°C 焊锡槽浸润 5±0.5秒	J-STD-002B
7	Drop Test (落下试验)	3 Times Free Fall from 75cm height table to 3cm thickness hard wood board 从75cm高度3次跌落到3cm厚硬质木板上	JIS C6701
8	MECHANICAL SHOCK (机械冲击)	Half sine wave, 1000 G 半正弦波, 加速度 1000G 3 Times for all 3 directions X、Y、Z 三个相互垂直方向各三次	MIL-STD-202F Method 213B
9	Vibration (机械振动)	Frequency Range: 10Hz~55Hz 频率范围: 10Hz~55Hz Amplitude: 0.75mm 振幅: 0.75mm 2 Hours in each direction, total 6 Hours X、Y、Z 三个相互垂直方向各振动2小时	MIL-STD-883E Method 2007.3
10	Leakage Test (气密性)	Take measurements with a helium Leakage detector 氦质检漏 Leakage Rate ≤ 1×10 ⁻³ Pa cm ³ /s 漏率 ≤ 1×10 ⁻³ Pa cm ³ /s	MIL-STD-883E