

### Features

- Wide supply voltage range from 2.0 V to 5.5 V
- CMOS low power dissipation
- High noise immunity
- Outputs Sink or Source 8 mA at VCC = 4.5V
- Packaging: TSSOP-14


### General Description

The 74AHC32 are quadruple 2-input positive-or gates which provides the function  $Y=A+B$  in positive logic.

### Applications

- Control indicator light LED
- Enable or disable digital signals
- Conversion between communication module and system controller

### PIN CONFIGURATIONS (Top view)



### PIN DESCRIPTION

| PIN NO. | PIN NAME | DESCRIPTION  | PIN NO. | PIN NAME | DESCRIPTION    |
|---------|----------|--------------|---------|----------|----------------|
| 1       | 1A       | Data input   | 8       | 3Y       | Data output    |
| 2       | 1B       | Data input   | 9       | 3A       | Data input     |
| 3       | 1Y       | Data output  | 10      | 3B       | Data input     |
| 4       | 2A       | Data input   | 11      | 4Y       | Data output    |
| 5       | 2B       | Data input   | 12      | 4A       | Data input     |
| 6       | 2Y       | Data output  | 13      | 4B       | Data input     |
| 7       | GND      | ground (0 V) | 14      | VCC      | supply voltage |

## Functional diagram




Fig. 1. Logic symbol




Fig. 2. IEC logic symbol




Fig. 3. Logic diagram(one gate)

## Function table

| Control |    | Output |
|---------|----|--------|
| nA      | nB | nY     |
| L       | L  | L      |
| L       | H  | H      |
| H       | L  | H      |
| H       | H  | H      |

Note: H=HIGH voltage level; L=LOW voltage level.

### ABSOLUTE MAXIMUM RATINGS

(Voltages are referenced to GND(ground=0V), unless otherwise specified.)

| Parameter               | Symbol    | Conditions                             | Min  | Max      | Unit |
|-------------------------|-----------|----------------------------------------|------|----------|------|
| Supply voltage          | $V_{CC}$  |                                        | -0.5 | +7       | V    |
| Input clamping current  | $I_{IK}$  | $V_I < -0.5V$ or $V_I > V_{CC} + 0.5V$ | --   | $\pm 20$ | mA   |
| Output clamping current | $I_{OK}$  | $V_O < -0.5V$ or $V_O > V_{CC} + 0.5V$ | --   | $\pm 20$ | mA   |
| Output current          | $I_O$     | $-0.5V < V_O < V_{CC} + 0.5V$          | --   | $\pm 25$ | mA   |
| Supply current          | $I_{CC}$  |                                        | --   | 50       | mA   |
| Ground current          | $I_{GND}$ |                                        | -50  | --       | mA   |
| Total power dissipation | $P_{tot}$ |                                        | --   | 500      | mW   |
| Storage temperature     | $T_{stg}$ |                                        | -65  | +150     | °C   |
| Soldering temperature   | $T_L$     |                                        | 260  |          | °C   |

### Recommended operating conditions

| Parameter                           | Symbol                | Conditions      | Min | Typ | Max      | Unit |
|-------------------------------------|-----------------------|-----------------|-----|-----|----------|------|
| Supply voltage                      | $V_{CC}$              |                 | 2.0 | --  | 5.5      | V    |
| Input voltage                       | $V_I$                 |                 | 0   | --  | $V_{CC}$ | V    |
| Output voltage                      | $V_O$                 |                 | 0   | --  | $V_{CC}$ | V    |
| Input transition rise and fall rate | $\Delta t / \Delta V$ | $V_{CC} = 3.3V$ | --  | --  | 100      | ns/V |
|                                     |                       | $V_{CC} = 4.5V$ | --  | --  | 60       | ns/V |
|                                     |                       | $V_{CC} = 5.5V$ | --  | --  | 20       | ns/V |
| Ambient temperature                 | $T_{amb}$             |                 | -40 | --  | +125     | °C   |

### Electrical Characteristics (DC)

( $T_{amb}=25^{\circ}\text{C}$ , voltages are referenced to GND (ground=0V), unless otherwise specified.)

| Parameter                 | Symbol   | Conditions                                   |                             | Min  | Typ  | Max       | Unit    |
|---------------------------|----------|----------------------------------------------|-----------------------------|------|------|-----------|---------|
| HIGH-level input voltage  | $V_{IH}$ | $V_{CC}=2.0V$                                |                             | 1.5  | --   | --        | V       |
|                           |          | $V_{CC}=3.0V$                                |                             | 2.1  | --   | --        | V       |
|                           |          | $V_{CC}=5.5V$                                |                             | 3.85 | --   | --        | V       |
| LOW-level input voltage   | $V_{IL}$ | $V_{CC}=2.0V$                                |                             | --   | --   | 0.5       | V       |
|                           |          | $V_{CC}=3.0V$                                |                             | --   | --   | 0.9       | V       |
|                           |          | $V_{CC}=5.5V$                                |                             | --   | --   | 1.65      | V       |
| HIGH-level output voltage | $V_{OH}$ | $V_I=V_{IH}$ or $V_{IL}$                     | $I_O=-50\mu A; V_{CC}=2.0V$ | 1.9  | 2.0  | --        | V       |
|                           |          |                                              | $I_O=-50\mu A; V_{CC}=3.0V$ | 2.9  | 3.0  | --        | V       |
|                           |          |                                              | $I_O=-50\mu A; V_{CC}=4.5V$ | 4.4  | 4.5  | --        | V       |
|                           |          |                                              | $I_O=-4.0mA; V_{CC}=3.0V$   | 2.58 | --   | --        | V       |
|                           |          |                                              | $I_O=-8.0mA; V_{CC}=4.5V$   | 3.94 | --   | --        | V       |
| LOW-level output voltage  | $V_{OL}$ | $V_I=V_{IH}$ or $V_{IL}$                     | $I_O=-50\mu A; V_{CC}=2.0V$ | --   | 0    | 0.1       | V       |
|                           |          |                                              | $I_O=-50\mu A; V_{CC}=3.0V$ | --   | 0    | 0.1       | V       |
|                           |          |                                              | $I_O=-50\mu A; V_{CC}=4.5V$ | --   | 0    | 0.1       | V       |
|                           |          |                                              | $I_O=-4.0mA; V_{CC}=3.0V$   | --   | 0.15 | 0.36      | V       |
|                           |          |                                              | $I_O=-8.0mA; V_{CC}=4.5V$   | --   | 0.16 | 0.36      | V       |
| Input leakage current     | $I_I$    | $V_I=V_{CC}$ or GND; $V_{CC}=5.5V$           |                             | --   | --   | $\pm 0.1$ | $\mu A$ |
| Supply current            | $I_{CC}$ | $V_I=V_{CC}$ or GND;<br>$I_O=0A;V_{CC}=5.5V$ |                             | --   | --   | 2.0       | $\mu A$ |
| Input capacitance         | $C_I$    |                                              |                             | --   | 4.0  | 10        | pF      |

### Electrical Characteristics (AC)

( $T_{amb}=25^{\circ}\text{C}$ , voltages are referenced to GND (ground=0V), unless otherwise specified.)

| Parameter                           | Symbol   | Conditions                                                   |                                       | Min | Typ | Max | Unit |
|-------------------------------------|----------|--------------------------------------------------------------|---------------------------------------|-----|-----|-----|------|
| nA, nB, to nY<br>propagation delay  | $t_{pd}$ | see Figure<br>5 <sup>[1]</sup>                               | $V_{CC}=2.0\text{V}$                  | --  | --  | 10  | ns   |
|                                     |          |                                                              | $V_{CC}=4.5\text{V}$                  | --  | --  | 10  | ns   |
|                                     |          |                                                              | $V_{CC}=5.0\text{V}; C_L=15\text{pF}$ | --  | 10  | --  | ns   |
|                                     |          |                                                              | $V_{CC}=6.0\text{V}$                  | --  | --  | 13  | ns   |
| Transition time                     | $t_t$    | see Figure<br>5 <sup>[2]</sup>                               | $V_{CC}=2.0\text{V}$                  | --  | --  | 7   | ns   |
|                                     |          |                                                              | $V_{CC}=4.5\text{V}$                  | --  | --  | 9   | ns   |
|                                     |          |                                                              | $V_{CC}=6.0\text{V}$                  | --  | --  | 9   | ns   |
| Power<br>dissipation<br>capacitance | $C_{PD}$ | per package;<br>$V_I = \text{GND to } V_{CC}$ <sup>[3]</sup> |                                       | --  | 14  | --  | pF   |

#### Note:

[1]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .

[2]  $t_t$  is the same as  $t_{THL}$  and  $t_{TLH}$ .

[3]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in

$\mu\text{W}$ ).  $P_D = (C_{PD} \times V_{CC}^2 \times f_i \times N) + \sum (C_L \times V_{CC}^2 \times f_o)$  where:

$f_i$ =input frequency in MHz;  $f_o$ =output

frequency in MHz;  $C_L$ =output load


capacitance in pF;  $V_{CC}$ =supply

voltage in V;  $N$ =number of inputs


switching;

$\sum (C_L \times V_{CC}^2 \times f_o)$ =sum of outputs.

## Testing Circuit




Note:  $C_L$  includes probe and jig capacitance.



### Voltage Waveforms Propagation Delays and Transition Times

## Package information

### TSSOP-14



| Symbol | Dimensions (mm) |      |
|--------|-----------------|------|
|        | Min.            | Max. |
| A      | -               | 1.20 |
| A1     | 0.05            | 0.15 |
| A2     | 0.80            | 1.05 |
| b      | 0.19            | 0.30 |
| c      | 0.09            | 0.20 |
| D      | 4.90            | 5.10 |
| E1     | 4.30            | 4.50 |
| E      | 6.20            | 6.60 |
| e      | 0.65            |      |
| L      | 0.45            | 0.75 |
| L1     | 1.00            |      |
| θ      | 0°              | 8°   |