


HIGH FREQUENCY LOW NOISE AMPLIFIER

DESCRIPTION

The **2SC3356** is designed for such applications as: DC/DC converters, supply line switching, battery charger, LCD backlighting, peripheral drivers, Driver in low supply voltage applications (e.g. lamps and LEDs) and inductive load driver (e.g. relays, buzzers and motors).

FEATURES

- * Low Noise and High Gain
- * High Power Gain





ORDERING INFORMATION

Ordering Number		Package	Pin Description			Packing
Lead Free	Halogen Free		1	2	3	
2SC3356		SOT-23-3	E	B	C	Tape Reel
2SC3356		SOT-23	E	B	C	Tape Reel

Note: Pin Assignment: B: Base C: Collector E: Emitter

MARKING

2SC3356		2SC3356	
	SOT-23-3		SOT-23

■ ABSOLUTE MAXIMUM RATING

PARAMETER	SYMBOL	RATINGS	UNIT
Collector to Base Voltage	BV_{CBO}	20	V
Collector to Emitter Voltage	BV_{CEO}	12	V
Emitter to Base Voltage	BV_{EBO}	3	V
Collector Current	I_C	100	mA
Power Dissipation	P_D	200	mW
Junction Temperature	T_J	150	°C
Storage Temperature	T_{STG}	-65~ +150	°C

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged.
Absolute maximum ratings are stress ratings only and functional device operation is not implied.







■ ELECTRICAL CHARACTERISTICS ($T_a=25^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Collector to Base Breakdown Voltage	BV_{CBO}	$I_C=10\mu\text{A}$, $I_E=0$	20			V
Collector to Emitter Breakdown Voltage	BV_{CEO}	$I_C=1\text{mA}$, $R_{BE}=\infty$	12			V
Emitter to Base Breakdown Voltage	BV_{EBO}	$I_E=10\mu\text{A}$, $I_C=0$	3			V
Collector-Base Cut-Off Current	I_{CBO}	$V_{CB}=10\text{V}$, $I_E=0$			1.0	μA
Emitter-Base Cut-Off Current	I_{EBO}	$V_{EB}=1\text{V}$, $I_C=0$			1.0	μA
DC Current Gain	h_{FE}	$V_{CE}=10\text{V}$, $I_C=20\text{mA}$	50		300	
Gain Bandwidth Product	f_T	$V_{CE}=10\text{V}$, $I_C=20\text{mA}$		6	7	GHz
Feed-Back Capacitance	C_{RE}	$V_{CB}=10\text{V}$, $I_E=0$, $f=1.0\text{MHz}$			1.0	pF
Noise Figure	NF	$V_{CE}=10\text{V}$, $I_C=7\text{mA}$, $f=1.0\text{GHz}$			2.0	dB

■ CLASSIFICATION OF h_{FE}

RANK	A	B	C
RANGE	50-160	160-240	240-300

■ **TYPICAL CHARACTERISTICS**



■ **TYPICAL CHARACTERISTICS(Cont.)**

