









ROHS



PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance	
Rated electrical load	DC 24V 8A
Contact resistance	≤0.03Ω
Insulation resistance	≥100MΩ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-40℃ - +85℃
service life	5000cycles



5	圆针	1	黄铜棒	镀银
4	盖片	1	H62黄铜带(Y)	镀银
3	簧片	1	磷铜带	铜锡
2	屏蔽罩	1	H62黄铜带(Y)	黑
1	基座	1	PPA	黑
序号	名称	数量	材料	备注

COSTOMER DRAWING		 深圳市莱联电子有限公司				
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE		DC电源连接器C2.0带屏蔽（弯插）	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-DC24-D6.5C2.0-W	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±3°	DWG.NO.	Projection 		