







技术指标:

1. 塑件表面应光洁, 无毛边, 无明显收缩, 缺陷, 裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ (含通电时的温度上升值).
3. 额定电压: 30V, AC/DC.
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min.
6. 额定电流: 0.5A, AC/DC
(使用AWG#28~#32, O.D 0.6mm MAX).
7. 耐电压: AC 200V/1分钟.

材质:

1. LCP 本色



Part No	CKT	A	B	C	D
WAFER-0.8-2PJK-GW	2	0.80	1.80	2.30	4.30
WAFER-0.8-3PJK-GW	3	1.60	2.60	3.10	5.10
WAFER-0.8-4PJK-GW	4	2.40	3.40	3.90	5.90
WAFER-0.8-5PJK-GW	5	3.20	4.20	4.70	6.70
WAFER-0.8-6PJK-GW	6	4.00	5.00	5.50	7.50
WAFER-0.8-7PJK-GW	7	4.80	5.80	6.30	8.30
WAFER-0.8-8PJK-GW	8	5.60	6.60	7.10	9.10
WAFER-0.8-9PJK-GW	9	6.40	7.40	7.90	9.90
WAFER-0.8-10PJK-GW	10	7.20	8.20	8.70	10.70
WAFER-0.8-11PJK-GW	11	8.00	9.00	9.50	11.50
WAFER-0.8-12PJK-GW	12	8.80	9.80	10.30	12.30
WAFER-0.8-13PJK-GW	13	9.60	10.60	11.10	13.10
WAFER-0.8-14PJK-GW	14	10.40	11.40	11.90	13.90
WAFER-0.8-15PJK-GW	15	11.20	12.20	12.70	14.70
WAFER-0.8-16PJK-GW	16	12.00	13.00	13.50	15.50
WAFER-0.8-17PJK-GW	17	12.80	13.80	14.30	16.30
WAFER-0.8-18PJK-GW	18	13.60	14.60	15.10	17.10
WAFER-0.8-19PJK-GW	19	14.40	15.40	15.90	17.90
WAFER-0.8-20PJK-GW	20	15.20	16.20	16.70	18.70
WAFER-0.8-21PJK-GW	21	16.00	17.00	17.50	19.50
WAFER-0.8-22PJK-GW	22	16.80	17.80	18.30	20.30
WAFER-0.8-23PJK-GW	23	17.60	18.60	19.10	21.10
WAFER-0.8-24PJK-GW	24	18.40	19.40	19.90	21.90
WAFER-0.8-25PJK-GW	25	19.20	20.20	20.70	22.70

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:

0.8 Pitch C型 WTB公头胶壳

PAR WAFER-0.8-NPJK-GW

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE:1:1 UNIT:MM

SIZE:A4

SHEET:1F1

REV:A

DECIMALS:

X.: ± 0.50 X.X: ± 0.20 X.XX: ± 0.10

ANGLES:

 $\pm 1^{\circ}$

CUSTOMER COPY

REV:A