







WITHOUT CAP



WITH CAP






AFTER MATING

**G-Switch USB-C Specification:**

1. Current rated: 5A on vbus/1.25A on vconn/0.25A on other
2. Voltage rating: 24V AC
3. Withstanding voltage: 100V AC/minute
4. Contact resistance: 40mΩ Max
5. Insulation resistance: 100MΩ Min
6. Operating temperature: -40°C ~ +85°C
7. Mating force: 5N~20N
8. Unmating force: 8N~20N, after durability test: 6N~20N
9. Durability cycle: 10,000 cycles
10. Data transmission rate up to 10Gbps
11. Compliant with: IEC62680-1-3

USB IF TID:15938


PCB REFERENCE DIAGRAM
TOLERANCE: ±0.05

SECTION A-A

CONTACT AREA	MOLDE CODE
Au1u"	GT-USB-9028G01-01
Au30u"	GT-USB-9028G01-30

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2-	RX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND	RX1+	RX1-	VBUS	SBU2	D-	D+	CC2	VBUS	TX2-	TX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First

NO.	PARTS	MATERIAL	REMARKS
1	SHELL	STAINLESS STEEL	NI30u"MIN PLATED
2	MID PLATE	STAINLESS STEEL	--
3	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK UL 94V-0
4	TERMINALS	COPPER ALLOY	Au PLATED ON CONTACT AREA Tin PLATED ON SOLDER AREA
5	GND PLATE	STAINLESS STEEL	--
6	CAP	HIGH TEMPERATURE PLASTIC	BLACK UL 94V-0



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.40
X.x ±0.30
X.xx ±0.20
X.xxx ±0.10
X" ±5°

Title: Vertical Type-C 24P Female
SMT H=14.00mm

Molde Code: GT-USB-9028G01-XX

DRAWN	CHECKED	APPROVED	DATE
Wu	Xia	Chen	2025.02.03

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1