






REV.	ECN NO.	DESCRIPTION	DRAW	DATE

Specification:


- 1.Electrical Characteristics:
Contact Current Rating:0.5 Amperes.
Dielectric Withstanding Voltage:AC500V r.m.s.
Insulation Resistance:1000 MΩ Minimum.
Contact Resistance:40 mΩ Maximum.
- 2.Environmental:
Operating Temperature:-25°C~+90°C.
- 3.Environmental:
Mating Cycles:5,000 Insertions.
- 4.Mechanical Characteristics:
Card Push Insertion/Out Force:0.2~1.40kgf.
Contact Separation Force:0.20kgf Minimum.
- 5.Material:
Insulator:HI-Temp Plastic UL 94V-0 Rated.
Contact:Copper Alloy(t=0.15mm).
Shell:Stainless Steel(t=0.15mm).
Spring:SWP.



PAD AREA
KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05



Circuit Diagram for Detect Switch



TF CARD PIN DEFINE			
PIN NO.	NAME	TYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(BIT1)


COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD					
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	自弹式 MicroSD卡(TF卡)卡座	REV.	A		
30-150	±0.35	PART NO.	LAIL-TF02-T1.8-T	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							

ROHS




纸箱规格:340*340*385

NO. 4



NO. 3

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



1. 材质要求:

- 1.1 纸箱的材质为K=K;外形尺寸为34*34*38.5;
- 1.2 卷盘的材质为PS,卷盘的外形尺寸为 $\phi 330 \times 30.4$;
- 1.3 卷带的材质为PS,卷带的外形尺寸为

20200*24.00*3.0mm;

2. 包装方式:

- 2.1 将卷带放入包装机后, 前空5PCS, 后放产品1000PCS, 再后空5PCS;上带留300MM长度。
- 2.2 将包装好的产品从包装机上取下并包装好, 贴上内盘标签;
- 2.3 把累叠好的12盘叠放入纸箱中共计12Kset, 上下放纸板, 纸箱四个角塞护角纸;
- 2.4 把包装好的成品打包封箱, 并在纸箱外贴上标签

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	自弹式 MicroSD卡(TF卡)卡座	REV.	A
30-150	±0.35	PART NO.	LAIL-TF02-T1. 8-T	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG.NO.		Projection	