



标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A



B


C



D


E

F




G

12.00



P=5.08*(N-1)



PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Solder pin: copper, nickel tin plated
- ③. Nut: Copper, Nickel Plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1min

mechanical properties

Temperature range: -40 ℃~+105 ℃

Instantaneous temperature: +250 ℃, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	品 名 TITLE	接线端子
公差参数		单 位 UNIT	MM	料 号 PART NO	HC-JXDZRM-5.08-6P
2-6P ±0.10 ±0.20		张 数 PART NO	1 OF 1	制 图 DRAW	AhYe
7-12P ±0.20 ±0.30		版 本 REV	A	审 核 CHECKED	夏操云
13-18P ±0.25 ±0.40				批 准 APPROVE	赵亮亮
19-24P ±0.30 ±0.50					

