






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



PCB LAYOUT

Materials and Electroplating

- ①. Plastic body: PA66
- ②. Solder pin: copper, nickel tin plated
- ③. Nut: Copper, Nickel Plated

Electrical performance

Rated voltage: 300V

Rated current: 15A

Contact resistance: 20m Ω (Max)

Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: -40 °C~+105 °C

Instantaneous temperature: +250 °C, 5 seconds

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	接线端子
			料 号 PART NO	HC-JXDZVM-5.08-16P
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
		单 位 UNIT	MM	
		张 数 PART NO	1 OF 1	审 核 CHECKED
		版 本 REV	A	批 准 APPROVE
		制 图 DRAW		夏操云
				赵亮亮

公差参数	公差	公差	公差
2-6P	±0.10	±0.20	X.xxx ±0.15
7-12P	±0.20	±0.30	X.xx ±0.25
13-18P	±0.25	±0.40	X.x ±0.35
19-24P	±0.30	±0.50	

