

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

Materials and Electroplating

- ①. Plastic body: PA66
②. Solder pin: copper, Nickel tin plating

Electrical performance

Rated voltage: 300V

Rated current: 8A

Contact resistance: 20m Ω (Max)





Insulation resistance: 500M Ω \ DC500V

Voltage endurance: AC1500V \ 1Min

mechanical properties

Temperature range: -40 ℃~+105 ℃

Instantaneous temperature:+250 ℃, 5 seconds



PCB LAYOUT

2	插针	铜	镀镍锡	
1	基座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE		接 线 端 子	
料 号 PART NO		HC-JXDZRC-3.81-5P	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1
单 位 UNIT		MM	制 图 DRAW
张 数 PART NO		1 OF 1	审 核 CHECKED
版 本 REV		A	批 准 APPROVE

公差参数		
尺寸	公差	公差
2-6P	±0.10	±0.20
7-12P	±0.20	±0.30
13-18P	±0.25	±0.40
19-24P	±0.30	±0.50

X.X ±0.35
X.XX ±0.25
X.XXX ±0.15

AhYe

夏操云

赵亮亮

